

Coaxial Adapter, BNC Tee Male / Female / Female

LCAD30012

Configuration

- BNC Male Connector 1
- BNC Female Connector 2

Features

- Provides In-Series BNC Connections
- Operates to 100 MHz

Applications

Description

These L-com RF Coaxial Adapters are used to interface between BNC to BNC with coaxial connections. The LCAD30012 is a tee adapter with a male to female configuration. This Coaxial Adapter, BNC Tee Male / Female / Female is made from brass and has a nickel finish.&&BNC adapters interface design is defined by Mil-STD-348A and has no tool required bayonet mount coupling mechanism with a robust center contact and outer conductor interface. BNC's generally work up to 3 GHz and are a cost effective way of insuring a highly dependable RF Coaxial connection.&&L-com's RF Coaxial and Triaxial adapters are in stock and ship same day.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|------------------------|---------|---------|---------|-------|
| Frequency Range | DC | | 100 | MHz |
| VSWR | | | 2.1:1 | |
| Operating Voltage (AC) | | | 500 | Vrms |
| | | | | |

Mechanical Specifications

| Size Length Width Height | | 1.56in 39.62mm] 0.9in [22.86mm] 0.57in [14.48mm] |
|--|-------------|--|
| Description | Connector 1 | Connector 2 |
| Туре | BNC Male | BNC Female |
| Polarity | Standard | Standard |
| | | |

Material Specifications

| Connector 1 Connector 2 | Connector 2 |
|-------------------------|-------------|
|-------------------------|-------------|



• Max VSWR of 2.1:1

• Impedance 50 Ohm

• Tee Body Geometry

Gold Plated Center Contacts



Coaxial Adapter, BNC Tee Male / Female / Female



LCAD30012

| Description | Material | Plating | Material | Plating |
|-----------------|----------|---------|------------|---------|
| Туре | BNC Male | | BNC Female | |
| Contact | Brass | Gold | Brass | Gold |
| Insulation | PTFE | | PTFE | |
| Outer Conductor | | | Brass | Nickel |
| Body | Brass | Nickel | Brass | Nickel |
| Gasket | Rubber | | | |
| Coupling Nut | Brass | Nickel | | |

Environmental Specifications

Temperature

Operating Range

-65°C to +165°C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Coaxial Adapter, BNC Tee Male / Female / Female from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

