

Coaxial Adapter, N Female / BNC Female 4 Hole Flange



LCAD30015

Configuration

- N Female Connector 1
- BNC Female Connector 2
- Impedance 50 Ohm

Features

- · Provides Between Series N to BNC Connections
- Operates to 6 GHz
- Max VSWR of 1.2:1
- **Applications**

- · Straight Body Geometry
- 4 Hole Flange Mount Method
- · Gold Plated Center Contacts
- 4 Hole Flange Mount

Description

These L-com RF Coaxial Adapters are used to interface between Type N to BNC with coaxial connections. The LCAD30015 is a straight 4 hole flange adapter with a female to female configuration. This Coaxial Adapter, N Female / BNC Female 4 Hole Flange is made from brass and has a nickel finish.&&The Type N interface design is defined by Mil-STD-348A and has many popular features including a threaded coupling method with a robust center contact and outer conductor interface. Type-N adapters generally operate to 12 GHz but precision versions will operate to 18 GHz. The larger size provides a very secure and robust interface and is often used as the output port on RF equipment. Type-N adapters are often used as port proetectors insuring that exepnsive test equipment ports are not damage during repeated use.&&BNC adapters interface design is defined by Mil-STD-348A and has no tool required bayonet mount coupling mechanism with a robust center contact and outer conductor interface. BNC's generally work up to 3 GHz and are a cost effective way of insuring a highly dependable RF Coaxial connection.&&L-com's RF Coaxial and Triaxial adapters are in stock and ship same day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.2:1	

Mechanical Specifications

 Size
 1.46in
 37.08mm

 Width
 1in
 [25.4mm]

Description	Connector 1	Connector 2
Туре	N Female	BNC Female
Polarity	Standard	Standard



Coaxial Adapter, N Female / BNC Female 4 Hole Flange



LCAD30015

Material Specifications

	Connector 1		Connector 2	
Description	Material	Plating	Material	Plating
Туре	N Female		BNC Female	
Contact	Beryllium Copper	Gold	Beryllium Copper	Gold
Insulation	PTFE		PTFE	
Outer Conductor	Brass	Nickel	Brass	Nickel
Body	Brass	Nickel	Brass	Nickel

Environmental Specifications

Temperature

Operating Range -65°C to +165°C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Coaxial Adapter, N Female / BNC Female 4 Hole Flange from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

