

Precision SMA Female to SMA Female Bulkhead Mount Adapter, With O-Ring



**LCAD9620**

**Configuration**

- SMA Female Connector 1
- SMA Female Connector 2
- Impedance 50 Ohm
- Precision Design
- Straight Body Geometry
- Bulkhead Mount Method

**Features**

- Max VSWR of 1.15:1 up to 18 GHz
- SMA Interface compliant with MIL-STD-348
- Gold Plated Beryllium Copper Contact

**Applications**

- General Purpose Test
- Rack Mounted Equipment
- Precision Test & Measurement

**Description**

The L-com LCAD9620 Precision adapter has a straight body geometry and is suitable for general-purpose test applications. This RF adapter has an SMA Female to SMA Female connector. The Female coaxial adapter has a Beryllium Copper contact.

This Precision adapter has an SMA interface compliant with MIL-STD-348 that brings interoperability of coaxial connectors, as well as a basis for the Hi-Rel design and construction of these components. The LCAD9620 coaxial adapter has Bulkhead mount and is suitable for rack-mounted equipment. This L-com connector RF adapter can operate at a temperature range of -55 to 125 deg C and has high repeatability.

The LCAD9620 coaxial adapter has a maximum frequency range of 18 GHz and is most used for Testing, Measurement, Satcom, Military, and Defense industries. This RF adapter has Gold plating and is designed to enable connections in RF and microwave systems between two of the same or different connector types. The L-com SMA adapter is constructed with a body and has no plating.

The SMA Female adapter is one of the thousands of RF products available from L-com in-stock inventory with same-day shipment for domestic and international orders. Make your online purchase right now for a high-quality 18 GHz coaxial adapter and take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the perfect Beryllium Copper RF adapter for your requirement.

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.15:1	

Precision SMA Female to SMA Female Bulkhead Mount Adapter, With O-Ring



**LCAD9620**

**Performance by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 4	4 to 8	8 to 18			GHz
VSWR, Max	1.05:1	1.1:1	1.15:1			

**Mechanical Specifications**

Size		
Length	0.875in	22.23mm]
Width	0.312in	[7.92mm]
Height	0.312in	[7.92mm]
Weight	0.0103lbs	[4.67g]

Description	Connector 1	Connector 2
Type	SMA Female	SMA Female
Polarity	Standard	Standard
Interface Specification	MIL-STD-348	MIL-STD-348

**Material Specifications**

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	SMA Female		SMA Female	
Contact	Beryllium Copper	Gold	Beryllium Copper	Gold
Outer Conductor	Passivated Stainless Steel		Passivated Stainless Steel	

**Environmental Specifications**

**Temperature**

Operating Range	-55°C to +125°C
-----------------	-----------------

## Precision SMA Female to SMA Female Bulkhead Mount Adapter, With O-Ring



**LCAD9620**

---

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Precision SMA Female to SMA Female Bulkhead Mount Adapter, With O-Ring from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# Precision SMA Female to SMA Female Bulkhead Mount Adapter, With O-Ring

## L-com CAD Drawing

