

902 to 928 MHz RFID Flat Panel Antenna, RHCP,  
8 dBi, White ABS, N Female, IP65



## LCANFP1032

### Features

- High Performance Multi-tag read/write Capabilities
- Concealable Design
- Right Hand Circular Polarized
- 902 to 928 MHz Frequency Range
- Type N Female Connector
- IP65 Rated

### Applications

- Radio Frequency Identification
- Inventory Management
- Access Control
- Data Collection
- Asset Tracking
- Livestock Management

### Description

L-Com's LCANFP1032 is a RHCP RFID flat panel antenna. The LCANFP1032 with a 8.5 dBi gain nominal is a Directional antenna. Our 902 to 928 MHz antenna has N Female connector and is IP65 Rated.

With an impedance of 50 Ohms and max input power of 50 Watts, the LCANFP1032 flat panel RHCP antenna is well suited for Radio Frequency Identification tag reading applications. This 902-928 MHz 8.5 dBi gain RFID antenna is highly directional providing the reader radio the capabilities of simultaneously reading a multitude of RFID tags with a high degree of accuracy.

L-Com's RFID LCANFP1032 has a radome made of ABS in White color. This N Female connectized Antenna has an overall length of 7.5 in, width of 7.5 in, and weighs 1.05 lbs. Use our on-line ordering system to purchase your LCANFP1032 RFID Directional RHCP antenna 24 hours a day with same-day shipping and no MOQs (minimum order quantities).

### Configuration

Design	Flat Panel
Application Band	RFID
Band Type	Single
Radiation Pattern	Directional
Polarization	RHCP
Connector Type	N Female
Lightning Protection	Direct Ground

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	902		928	MHz
Input VSWR			1.4:1	
Impedance		50		Ohms
Gain		8.5		dBi
Horizontal (Azimuth) HPBW		65		Degrees
Vertical (Elevation) HPBW		72		Degrees
Input Power			50	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:  
[902 to 928 MHz RFID Flat Panel Antenna, RHCP, 8 dBi, White ABS, N Female, IP65 LCANFP1032](#)

902 to 928 MHz RFID Flat Panel Antenna, RHCP,  
8 dBi, White ABS, N Female, IP65



## LCANFP1032

Axial Ratio	3	dB
-------------	---	----

### Mechanical Specifications

Radome Material	ABS
<b>Size</b>	
Length	7.5 in [190.5 mm]
Width	7.5 in [190.5 mm]
Height	1 in [25.4 mm]
Weight	0.8 lbs [362.87 g]

### Environmental Specifications

<b>Temperature</b>	
Operating Range	-40 to +55 deg C
Ingress Protection	IP65

**Compliance Certifications** (see [product page](#) for current document)


### Plotted and Other Data

Notes:

902 to 928 MHz RFID Flat Panel Antenna, RHCP, 8 dBi, White ABS, N Female, IP65 from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing



NOTES:

- LABEL PER ILS-100-03 (FOR INTERNAL USE ONLY)  
LABEL LOCATION SHOWN FOR REFERENCE ONLY

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

**L-com**  
an INFINITE brand

50 High Street, West Mill, 3rd Floor, Suite #30  
North Andover, MA 01845, USA.  
Phone: 1.800.341.5266 | 1.978.682.6936  
Fax: 1.978.689.9484  
Website: www.L-com.com  
E-mail: CustomerService@L-com.com

THIRD-ANGLE PROJECTION

THE INFORMATION AND DRAWING CONTENT IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

SIZE	CAGE CODE	DRAWN BY	ITEM NO.
A	43321	BPUCHASKI	LCANFP1032
REV			A

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:

.X = ±.2	[5.08]	FRACTIONS	± 1/32
.XX = ±.02	[.51]		
.XXX = ±.005	[.13]	ANGLES	± 1°

CABLE LENGTH (L) TOLERANCES:

L ≤ 12 [305]	± 1 [25] / -0
12 [305] < L ≤ 60 [1524]	± 2 [51] / -0
60 [1524] < L ≤ 120 [3048]	± 4 [102] / -0
120 [3048] < L ≤ 300 [7620]	± 6 [152] / -0
300 [7620] < L ≤ ∞	± 5% L / -0

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.