

800 MHz to 2.7 GHz LTE Antenna, Tilt and Swivel,
Monopole, SMA Male Connector, 3 dBi Gain



LCANRBD1054

Features

- 800-960 / 1710-2170 / 2400-2700 MHz, 3 dBi Gain
- SMA male connector
- Plug and play
- VSWR < 3.5:1
- Linear polarization
- Monopole antenna

Applications

- 4G LTE applications
- Wireless communications
- IOT sensors and trackers
- Wireless microphones
- Remote control
- Industrial monitoring and data transmission
- Amateur radio
- 2.4 GHz Wi-Fi and ISM applications
- 802.11 a/b/g/n/ax, wireless hotspots
- 5G bands: n1, n2, n3, n5, n7, n8, n18, n20, n25, n26, n34, n38, n39, n41, n53, n65, n81, n82, n84, n89, n90, n91, n92, n93, n94, n95, n98, n100, n101
- 4G LTE bands: B1, B2, B3, B4, B5, B6, B7, B8, B9, B10, B18, B19, B20, B23, B25, B26, B27, B34, B35, B36, B37, B38, B39, B41, B65, B66, B69, B70

Description

The L-com LCANRBD1054 is an omni antenna operating from 800 MHz to 2.7 GHz with 3 dBi gain. The SMA male connector on the communication antenna enables it to be used vertically or at any angle in between. Our rubber duck antenna is 0.37 inches wide, 2.8 inches long, and 0.37 inches tall. Our tilt-and-swivel LTE antenna is specifically stocked to be available for same business day shipment.

This monopole omnidirectional antenna has a linear polarization and an SMA male connector. Our 3 dBi gain LCANRBD1054 antenna transmits high power signals, increasing the signal strength, thus providing improved coverage, better broadcast control, and faster speed. L-com single-band antenna has a gain of 3 dBi antenna for the 800 MHz to 2.7 GHz frequency range. Our black omnidirectional antenna functions between -40 to 70 degrees C and has 50 Ohm impedance.

L-com WiFi antenna is ideal for 4G LTE applications, public safety, security, construction, wireless communications, IOT applications, RFID, 2.4 GHz Wi-Fi and ISM applications, bluetooth, industrial monitoring and data transmission, remote control, and amateur radio. These 3 dBi antennas have a sturdy design and a high power handling capacity. Our high-quality LCANRBD1054 omnidirectional antenna has a maximum input VSWR of 4:1, which results in the best power transfer and reduced losses.

The 3 dBi gain omni directional antenna is just one of many fiber optic products that are available from L-com for international and domestic orders. We are a global leader in wired and wireless connectivity products, offering a wide range of solutions across many key industries, including electronics, medical, industrial automation, military, and telecommunication. L-com also stocks a wide selection of 800 MHz to 2.7 GHz antennas that ship same-day from our warehouse.

Configuration

Design	Rubber Duck
Band Type	Multi
Radiation Pattern	Omni Directional
Polarization	Linear
Connector Type	SMA Male

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[800 MHz to 2.7 GHz LTE Antenna, Tilt and Swivel, Monopole, SMA Male Connector, 3 dBi Gain LCANRBD1054](#)

800 MHz to 2.7 GHz LTE Antenna, Tilt and Swivel,
Monopole, SMA Male Connector, 3 dBi Gain



LCANRBD1054

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	800		2,700	MHz
Impedance		50		Ohms
Input Power			10	Watts

Specifications by Band

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	0.8-0.96	1.71-2.17	2.4-2.7			GHz
Gain	2.5	3.5	3			dBi
VSWR Max	2.5:1	3.5:1	3.5:1			

Mechanical Specifications

Radome Material	ABS
Size	
Length	2.8 in [71.12 mm]
Width	0.37 in [9.4 mm]
Height	0.37 in [9.4 mm]
Weight	0.01804 lbs [8.18 g]

Environmental Specifications

Temperature	
Operating Range	-40 to +70 deg C
Storage Range	-40 to +70 deg C
Environment	Waterproof
Ingress Protection	IP65

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

800 MHz to 2.7 GHz LTE Antenna, Tilt and Swivel, Monopole, SMA Male Connector, 3 dBi Gain from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and

800 MHz to 2.7 GHz LTE Antenna, Tilt and Swivel,
Monopole, SMA Male Connector, 3 dBi Gain

LCANRBD1054



active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

800 MHz to 2.7 GHz LTE Antenna, Tilt and Swivel, Monopole, SMA Male Connector, 3 dBi Gain

L-com CAD Drawing

