

4.9 GHz to 5.8 GHz 22 dBi Lightweight Die-cast
Grid Antenna Type N Female Connector



HG4922EG-1-NF

Features

- All weather operation
- Easy to assemble
- UV stable powder coat finish
- Die-cast aluminum construction
- High Gain

Applications

- 5 GHz ISM applications
- Long-range Directional Applications
- 5 GHz UNII applications
- Point to Point (PtP) and Multipoint to Point (MPtP)
- 5 GHz Wireless LAN system

Description

The L-com HG4922EG-1-NF is a high-performance light weight reflector grid antenna specifically designed for long-range directional point to point systems, point to multipoint and wireless bridges. L-com's HG4922EG-1-NF has 20 to 22 dBi gain. The HG4922EG-1-NF operates from 4900 to 5850 MHz which is ideal for WLAN backhaul.

The HG4922EG-1-NF from L-com has 12° Vertical and 9° Horizontal Beamwidth patterns with vertical or horizontal polarization and features Type N female connectors. The 4900-5850 MHz HG4922EG-1-NF is shipped as a 2-piece reflector grid which is simple to assemble and greatly reduces shipping costs.

The Type N female connectorized HG4922EG-1-NF antenna from L-com has mounting bracket and hardware included which makes this antenna very easy to install. This high-performance light weight reflector grid antenna just like our wide selection of superior quality RF parts, ship same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other L-com products.

Configuration

Design	Grid
Polarization	Vertical
Connector Type	N Female

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	4.9		5.85	GHz
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain		22		dBi
Front to Back Ratio	20			dB
Horizontal (Azimuth) HPBW		9		Degrees
Vertical (Elevation) HPBW		12		Degrees
Input Power			100	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[4.9 GHz to 5.8 GHz 22 dBi Lightweight Die-cast Grid Antenna Type N Female Connector HG4922EG-1-NF](#)

4.9 GHz to 5.8 GHz 22 dBi Lightweight Die-cast
Grid Antenna Type N Female Connector



HG4922EG-1-NF

Mechanical Specifications

Size

Length	11.811 in [300 mm]
Width	15.748 in [400 mm]
Height	20 in [508 mm]
Mounting Mast Diameter	1.57 to 1.96 in [39.88 to 49.78 mm]
Weight	3.08647 lbs [1.4 kg]

Environmental Specifications

Temperature

Operating Range	-40 to +70 deg C
Wind Survivability	124 MPH [199.56 KPH]
Humidity	5 to 95 %

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

4.9 GHz to 5.8 GHz 22 dBi Lightweight Die-cast Grid Antenna Type N Female Connector from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

4.9 GHz to 5.8 GHz 22 dBi Lightweight Die-cast Grid Antenna Type N Female Connector

L-com CAD Drawing

