

698 MHz-960 MHz / 1710 MHz-2700 MHz, 1-3 dBi, IP67, 4G LTE Cellular portable rubber duck antenna, RIGID SMA male connector

### HG72703RDR-SM



#### **Features**

- IP67 Ruggedized Waterproof Design
- 0 to 4 dBi gain

# Rigid SMA Male Connector

### **Applications**

- Infotainment Systems, Routers, WiFi Hotspots, HD Video Trans 4G & 5G Networks
   700, 850, 900, 1800, 1900, 2100, 2600 MHz Bands
  - Connected Cars or Self-Driving Cars, Fleet Management, Logis- IoT, Cellular, Zigbee, Z-Wave, Bluetooth

## tics

**Description** 

The HG72703RDR-SM 4G Rubber Duck Antenna from L-com is a high performance omnidirectional "rubber-duck" antenna. This rubber duck is designed for the 698 MHz to 2700 MHz bands and is available to ship same day. It features a RIGID SMA-Plug (male) connector. This straight SMA allows the HG72703RDR-SM to be mounted directly to terminals and other fixed radios. It is a coaxial sleeve design with an omni-directional pattern. The HG72703RDR-SM is ideally suited for 4G, LTE, IoT, Zigbee, Zwave and Bluetooth bands.

The L-com high performance rubber-duck HG72703RDR-SM is a rubber coated RIGID antenna providing broad coverage and 3 dBi gain. This SMA RIGID male rubber duck is suitable for commercial radios in public and private 4G and Cellular networks that are equipped with SMA female connectors. L-com's HG72703RDR-SM supports 700, 800, 850, 900, 1800, 2100, 2400, and 2600 MHz bands.

This 4G 698 MHz to 2700 MHz rubber duck antenna with a SMA male straight connector, as well as our wide selection of superior quality RF parts, ships same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other L-com products.

### Configuration

Design
Band Type
Radiation Pattern
Wavelength
Polarization

Connector Type

Portable Dual

Omni Directional

1/2 Vertical SMA Male

### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	698		2,700	MHz
Input VSWR		2:1	4.5:1	
Impedance		50		Ohms
Gain		3		dBi
Gain	1			dBi
Horizontal (Azimuth) HPBV	V	360		Degrees

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 698 MHz-960 MHz / 1710 MHz-2700 MHz, 1-3 dBi, IP67, 4G LTE Cellular portable rubber duck antenna, RIGID SMA male connector HG72703RDR-SM



698 MHz-960 MHz / 1710 MHz-2700 MHz, 1-3 dBi, IP67, 4G LTE Cellular portable rubber duck antenna, RIGID SMA male connector



### HG72703RDR-SM

Vertical (Elevation) HPBW	45		Degrees
Input Power		5	Watts

## Specifications by Band

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	0.698 to 0.96	1.71 to 2.7				GHz
Gain	1	3				dBi
Horizontal HPBW	360	360				Degrees
Vertical HPBW	60	45				Degrees
VSWR Max	4.5:1	2:1				

### **Mechanical Specifications**

Radome Material PU

 Width
 0.39 in [9.91 mm]

 Height
 2.1 in [53.34 mm]

 Weight
 0.19 lbs [86.18 g]

### **Environmental Specifications**

**Temperature** 

Operating Range -20 to +65 deg C
Storage Range -30 to +70 deg C
Environment Waterproof

Humidity 95%

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

698 MHz-960 MHz / 1710 MHz-2700 MHz, 1-3 dBi, IP67, 4G LTE Cellular portable rubber duck antenna, RIGID SMA male connector from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# **L-com CAD Drawing**

