

698-960 MHz / 1710-2700 MHz / 3400-4200 MHz Low PIM Rated VH-pol MIMO Panel Antenna, 5-7 dBi, Wall Mount, 2 x 4.3-10 Female Connector

# HG74207DPPR-4310F



#### **Features**

- Low Passive Intermodulation (PIM) <-153 dBc @ 2x20W</li>
- Vertical + Horizontal Polarization
- · Low return loss, stable performance

# **Applications**

- Indoor distribution of 5G, LTE, GSM/CDMA
- · In-building public or private networks
- LPWAN, LoRA, LTE-M, NB-IoT, IoT, M2M applications
- 2 x 4.3-10 Female connector for long lasting consistent results
- Covers 5G, WiFi and LTE frequency bands including extended CBRS
- MIMO DAS (Distributed Antenna Systems)
- Wall Mounts

# Description

The L-com HG74207DPPR-4310F is a low PIM rated, high performance wall mount MIMO panel antenna specifically designed for inbuilding wireless networks such as DAS (Distributed Antenna Systems). L-com's HG74207DPPR-4310F has 5 to 7 dBi gain and can be used to distribute Cellular and WiFi signals throughout a building or area. The HG74207DPPR-4310F operates from 698 to 4200 MHz which is ideal for 5G, LTE, CDMA, LPWAN/IoT/M2M applications including LoRA, LTE-M, and NB-IOT. The Multi-Band design of the L-com HG74207DPPR-4310F antenna eliminates the need to purchase different antennas for each frequency. This simplifies installations since the same antenna can be used for a wide array of in-building wireless applications where wide coverage is desired.

The HG74207DPPR-4310F from L-com has directional 75 degree typical patterns with V/H polarization and features 4.3-10 connectors. The key to providing the best performance in telecommunications is to ensure the components used are low PIM rated. This helps meet the increasing demand for higher data rates and the ability to provide streaming video for mobile devices. With a low PIM rating of <-150 dBc, the 698-4200 MHz HG74207DPPR-4310F helps meets the most demanding PIM requirements for 5G and LTE/4G bands.

The 4.3-10 connectorized HG74207DPPR-4310F antenna from L-com is designed specifically for in-building operation and is ideal for use in large open areas such as indoor courtyards, indoor sporting venues, convention centers and shopping malls. The included mounting bracket and hardware makes this antenna very easy to install. This 5G Cellular antenna just like our wide selection of superior quality RF parts, ship same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other L-com products.

# Configuration

Design Band Type Radiation Pattern Polarization Connector Type Interface 2 Number of Ports Panel Wide Directional Vertical/Horizontal 4.3-10 Female 4.3-10 Female

# **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	698		4200	MHz
Input VSWR			2:1	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 698-960 MHz / 1710-2700 MHz / 3400-4200 MHz Low PIM Rated VH-pol MIMO Panel Antenna, 5-7 dBi, Wall Mount, 2 x 4.3-10 Female Connector



698-960 MHz / 1710-2700 MHz / 3400-4200 MHz Low PIM Rated VH-pol MIMO Panel Antenna, 5-7 dBi, Wall Mount, 2 x 4.3-10 Female Connector

### HG74207DPPR-4310F

Impedance	50		Ohms
Gain	5		dBi
Gain Input Power		7	dBi
Input Power		100	Watts
Passive Intermodulation	-153		
3rd Order. 2 x 20 W			

# Specifications by Band

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	0.698 to 0.806	0.806 to 0.96	1.71 to 2.7	3.4 to 4.2		GHz
Gain	5	6	7	7		dBi
Horizontal HPBW	80	80	65	35		Degrees
Vertical HPBW	73	70	60	30		Degrees
VSWR Max	2:1	2:1	2:1	2:1		

# **Mechanical Specifications**

Radome Material PVC

Size

 Length
 15.75 in [400.05 mm]

 Width
 7.09 in [180.09 mm]

 Height
 2.44 in [61.98 mm]

 Weight
 3.3 lbs [1.5 kg]

### **Environmental Specifications**

**Temperature** 

Operating Range -55 to +60 deg C

Humidity < 95

Compliance Certifications (see product page for current document)

# **Plotted and Other Data**

Notes:

698-960 MHz / 1710-2700 MHz / 3400-4200 MHz Low PIM Rated VH-pol MIMO Panel Antenna, 5-7 dBi, Wall Mount, 2 x 4.3-10 Female Connector from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies,



698-960 MHz / 1710-2700 MHz / 3400-4200 MHz Low PIM Rated VH-pol MIMO Panel Antenna, 5-7 dBi, Wall Mount, 2 x 4.3-10 Female Connector

### HG74207DPPR-4310F



connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# **L-com CAD Drawing**

