

HyperLink Wireless brand 2.4 GHz 6 dBi High Performance Omni-directional Wireless LAN Antenna - HyperGain<sup>®</sup> Model: HGV-2406U

# **Applications and Features**

Applications:	<ul> <li>2.4 GHz ISM Band</li> <li>IEEE 802.11b and 802.11g Wireless LAN</li> <li>Bluetooth<sup>®</sup></li> <li>Public Wireless Hotspot</li> <li>WiFi</li> <li>Multipoint and Mobile Applications</li> </ul>	
Features:	<ul> <li>High performance</li> <li>Economical</li> <li>Compact, lightweight design</li> <li>Durable UV-stable fiberglass radome</li> <li>Vented end cap and drain holes in base</li> <li>All weather operation</li> <li>Integral N-Female connector</li> <li>Can be installed in up or down positions</li> <li>Includes Mast Mounting Kit</li> <li>RoHS Compliant</li> </ul>	

## Description

#### **High Performance**

The HyperGain<sup>®</sup> Model HGV-2406U is and economical yet high performance Omni-directional WiFi antenna designed for the 2.4GHz ISM band. These compact and lightweight antennas are ideally suited for IEEE 802.11b and 802.11g wireless LANs, Bluetooth, public wireless hotspot application and other multipoint applications where wide coverage is desired.


### **Versatile and Economical**

This antenna features an integral N-Female bulkhead type connector that mounts through the wall of an equipment enclosure. Included with the HGV-2406U is a mast mounting kit. Consisting of a heavy-duty steel bracket and a pair of U-bolts, this kit allows installation on masts up to 2.0" in diameter.



### **All Weather Operation**

Constructed for all weather operation, the HGV-2406U features sealed collinear brass elements inside a durable UV-stable machine gray fiberglass radome. A vented end cap and drain holes in the base help prevent moisture build-up inside the antenna. These features allow the HGV-2406U to be mounted in up or down positions.




L-com, Inc. 50 High St., West Mill, 3<sup>rd</sup> Floor, Suite #30 North Andover, MA 01845 www.L-com.com E-mail: sales@L-com.com Phone: 1-800-343-1455 Fax: 1-978-689-9484 © L-com, Inc. All Rights Reserved. L-com Global Connectivity and the L-com logo are registered marks.



## Specifications

Frequency	2400-2500 MHz	
riequency	2400-2300 1112	
Gain	6 dBi	
Polarization	Vertical	
Vertical Beam Width	28 °	
Horizontal Beam Width	360°	
Impedance	50 Ohm	
Max. Input Power	100 Watts	
VSWR	< 1.5:1 avg.	
Weight	.24 lbs. (0.1 kg)	
Length	12 in. (30 cm)	
Base Diameter	1.27 in. (3.22 cm)	
Radome Diameter	.75 in. (1.90 cm)	
Radome Material	Gray Fiberglass	
Wind Survival	>150 MPH	
Operating Temperature	-40° C to 85° C (-40° F to 185° F)	
Connector	Integral N-Type Female (Bulkhead type)	
RoHS Compliant	Yes	

### **RF Antenna Gain Pattern**



## **Guaranteed Quality**

This product is backed by Hyperlink's Limited Warranty.

## **Mounting Options**

