

Coaxial Adapter, N Female / BNC Female

LCAD30014

Configuration

- N Female Connector 1
- BNC Female Connector 2

Features

- · Provides Between Series N to BNC Connections
- · Operates to 3 GHz

Applications

Description

These L-com RF Coaxial Adapters are used to interface between Type N to BNC with coaxial connections. The LCAD30014 is a straight adapter with a female to female configuration. This Coaxial Adapter, N Female / BNC Female is made from brass and has a nickel finish.&&The Type N interface design is defined by Mil-STD-348A and has many popular features including a threaded coupling method with a robust center contact and outer conductor interface. Type-N adapters generally operate to 12 GHz but precision versions will operate to 18 GHz. The larger size provides a very secure and robust interface and is often used as the output port on RF equipment. Type-N adapters are often used as port protectors insuring that exepnsive test equipment ports are not damage during repeated use.&&BNC adapters interface design is defined by Mil-STD-348A and has no tool required bayonet mount coupling mechanism with a robust center contact and outer conductor interface. BNC's generally work up to 3 GHz and are a cost effective way of insuring a highly dependable RF Coaxial connection.&&L-com's RF Coaxial and Triaxial adapters are in stock and ship same day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
Operating Voltage (AC)			500	Vrms
Inner Conductor DC Resistar	ice		1.5	mOhms
Outer Conductor DC Resista	nce		1	mOhms
Insulation Resistance	5,000			MOhms

Mechanical Specifications

1

Size Length Width		1.1in 27.94mm] 0.62in [15.75mm]
Description	Connector 1	Connector 2
Туре	N Female	BNC Female
Polarity	Standard	Standard

- Impedance 50 Ohm
- Straight Body Geometry
- · Gold Plated Center Contacts



Coaxial Adapter, N Female / BNC Female



LCAD30014

Material Specifications

Material			
	Plating	Material	Plating
N Female		BNC Female	
Brass	Gold	Brass	Gold
PTFE		PTFE	
Brass	Nickel	Brass	Gold
Brass	Nickel	Brass	Nickel
	Brass PTFE Brass	Brass Gold PTFE Brass Nickel	BrassGoldBrassPTFEPTFEBrassNickelBrass

Environmental Specifications

Temperature

Operating Range

-65°C to +165°C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Coaxial Adapter, N Female / BNC Female from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

