

Coaxial Right Angle Adapter, 78 Ohm BNC Twinax Plug / Jack

LCAD30025

Configuration

- BNC Twinax Plug Connector 1
- BNC Twinax Jack Connector 2

• Impedance 78 Ohm

• Right Angle Body Geometry

Right Angle Body Geometry

Features

- Provides In-Series BNC to BNC Connections
- Gold Plated Center Contacts

Applications

Description

These L-com RF Coaxial Adapters are used to interface between BNC Twinax to BNC Twinax with coaxial connections. The LCAD30025 is a right angle adapter with a plug to jack configuration. This Coaxial Right Angle Adapter, 78 Ohm BNC Twinax Plug / Jack is made from brass and has a nickel finish.&&The Twin-Ax BNC has twn contacts inside the connector housing. The coupling mechanism is a boyonet design, the same as a standard BNC. Twin-ax BNC connections are commanly used with Twin-ax cable used in differential pair applications where separate conductors are used to carry the signal of interest. BNC Twinax adapters are ofen required to adapt between connector genders.&&L-com's RF Coaxial and Triaxial adapters are in stock and ship same day.

Mechanical Specifications

Size Length Width Height		1.02in 0.57in 89in	25.91mm] [14.48mm] [226.06cm]	
Description	Connector 1		Connector 2	
Туре	BNC Twinax Plug	BNC Twinax Jack		
Polarity	Standard	Standard		

Material Specifications

connector 1

Connector 2





Coaxial Right Angle Adapter, 78 Ohm BNC Twinax Plug / Jack



LCAD30025

Description	Material	Plating	Material	Plating
Туре	BNC Twinax Plug		BNC Twinax Jack	
Contact	Brass	Gold	Brass	Gold
Insulation	Delrin		Delrin	
Outer Conductor			Brass	Gold
Body	Brass	Nickel	Brass	Nickel
Gasket	Rubber		Rubber	
Coupling Nut	Brass	Nickel		

Environmental Specifications

Temperature

Operating Range

-65°C to +165°C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Coaxial Right Angle Adapter, 78 Ohm BNC Twinax Plug / Jack from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representative of the part described herein. It may be necessary to make modifications to the part and/or the document is accurate to the best of our knowledge and representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

