

Coaxial Adapter, BNC Male / RP-BNC Female



## LCAD30029

### Configuration

- BNC Male Connector 1
- BNC Female Reverse Polarity Connector 2
- Impedance 50 Ohm
- Straight Body Geometry

### Features

- Provides In-Series BNC to Reverse Polarity BNC Connections
- Gold Plated Center Contacts

### Applications

### Description

These L-com RF Coaxial Adapters are used to interface between BNC to BNC with coaxial connections. The LCAD30029 is a straight adapter with a male to female configuration. This Coaxial Adapter, BNC Male / RP-BNC Female is made from brass and has a nickel finish. BNC adapters interface design is defined by Mil-STD-348A and has no tool required bayonet mount coupling mechanism with a robust center contact and outer conductor interface. BNC's generally work up to 3 GHz and are a cost effective way of insuring a highly dependable RF Coaxial connection. L-com's RF Coaxial and Triaxial adapters are in stock and ship same day.

### Mechanical Specifications

<b>Size</b>			
Length	1.23in	31.24mm]	
Width	0.57in	[14.48mm]	

Description	Connector 1	Connector 2
Type	BNC Male	BNC Female
Polarity	Standard	Reverse Polarity

### Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	BNC Male		BNC Female Reverse Polarity	
Contact	Brass	Gold	Brass	Gold
Insulation	PTFE		PTFE	
Outer Conductor			Brass	Nickel
Body	Brass	Nickel	Brass	Nickel
Gasket			Silicone	
Coupling Nut	Brass	Nickel		

Coaxial Adapter, BNC Male / RP-BNC Female



**LCAD30029**

---

## Environmental Specifications

### Temperature

Operating Range -65°C to +165°C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Coaxial Adapter, BNC Male / RP-BNC Female from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Coaxial Adapter, BNC Male / RP-BNC Female

L-com CAD Drawing

REVISIONS		
REV.	DESCRIPTION	DATE
A	INITIAL RELEASE	01/15/2020
		APPROVED SELLIS

  

Technical drawing of a coaxial adapter. The drawing shows a side view of the component with the following dimensions: a diameter of  $\Phi .57$  [14.5] at the base, a total length of 1.23 [31.3], and a small feature width of .4 [1.1].

  

<p>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS</p> <p><b>TOLERANCES:</b></p> <p>X = ±.2 [5.08]   FRACTIONS ± 1/32   ANGLES ± 1°          .XX = ±.005 [ .13 ]          .XXX = ±.001 [ .025 ]</p> <p><b>CABLE LENGTH (L) TOLERANCES:</b></p> <p>L ≤ 12 [305] = +1 [25] / -0          12 [305] &lt; L ≤ 60 [1524] = +2 [51] / -0          60 [1524] &lt; L ≤ 120 [3048] = +4 [102] / -0          120 [3048] &lt; L ≤ 300 [7620] = +6 [152] / -0          300 [7620] &lt; L = +5% / -0</p> <p>ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.</p>	<p><b>L-com™</b>  <b>an INFINITE brand</b>          50 High Street, West Mill, 3rd Floor, Suite #30          North Andover, MA 01845 USA.          Phone: 1.800.341.5266   1.978.682.6936          Fax: 1.978.689.9484          Website: www.L-com.com          E-mail: CustomerService@L-com.com</p>	<p>THIRD-ANGLE PROJECTION</p> <p>THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED.</p> <p>SHEET 1 OF 1          SCALE N/A</p>
<p>SIZE A</p>	<p>CASE CODE 43321</p>	<p>DRAWN BY BPUCHASKI</p>
<p>PART NUMBER LCAD30029</p>	<p>REV A</p>	

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.