

3.3 GHz to 3.8 GHz Blade Style Antenna, Dipole, SMA Male Connector, 4.5 dBi Gain

### LCANRBD1052



### **Features**

- · 3300-3800 MHz, 4.5 dBi Gain
- · SMA male connector
- · Plug and play

# **Applications**

- · CBRS application range
- WISP applications
- 5G wireless network
- · Remote monitoring
- · Telemedicine, disaster response

- VSWR < 2:1</li>
- · Vertical polarization
- · Dipole antenna
- RFID
- · Surveillance systems
- · Broadcasting equipment addition
- 5G bands: n48, n77, n78
- 4G LTE bands: B22, B42, B43, B48, B49, B52

# **Description**

The L-com LCANRBD1052 is an omni antenna operating from 3.3 GHz to 3.8 GHz with 4.5 dBi gain. The SMA male connector on the communication antenna enables it to be used vertically or at any angle in between. Our rubber duck antenna is 0.86 inches wide, 8.19 inches long, and 0.51 inches tall. Our blade-style omni antenna is specifically stocked to be available for same business day shipment.

This dipole omnidirectional antenna has a vertical polarization, an SMA male connector and an ABS radome material. Our 4.5 dBi gain LCANRBD1052 antenna transmits high power signals, increasing the signal strength, thus providing improved coverage, better broadcast control, and faster speed. L-com single-band antenna has a gain of 4.5 dBi antenna for the 3.3 GHz to 3.8 GHz frequency range. Our black omnidirectional antenna functions between -20 to 65 degrees C and has 50 Ohm impedance.

L-com WiFi antenna is ideal for CBRS application range, WISP applications, 5G wireless network, remote monitoring, telemedicine, disaster response, RFID, surveillance systems, and broadcasting equipment addition. These 4.5 dBi antennas have a sturdy design and a high power handling capacity. Our high-quality LCANRBD1052 omnidirectional antenna has a maximum input VSWR of 2:1, which results in the best power transfer and reduced losses.

The 4.5 dBi gain omni directional antenna is just one of many fiber optic products that are available from L-com for international and domestic orders. We are a global leader in wired and wireless connectivity products, offering a wide range of solutions across many key industries, including electronics, medical, industrial automation, military, and telecommunication. L-com also stocks a wide selection of 3.3 GHz to 3.8 GHz antennas that ship same-day from our warehouse.

### Configuration

Design Band Type Radiation Pattern Polarization Connector Type Rubber Duck Single Omni Directional Vertical SMA Male

### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units	
Frequency Range	3,300		3,800	MHz	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 3.3 GHz to 3.8 GHz Blade Style Antenna, Dipole, SMA Male Connector, 4.5 dBi Gain LCANRBD1052



3.3 GHz to 3.8 GHz Blade Style Antenna, Dipole, SMA Male Connector, 4.5 dBi Gain

# LCANRBD1052

nput VSWR		2:1	
Input VSWR Impedance Gain	50		Ohms
Gain	4.5		dBi
Input Power		10	Watts

# **Mechanical Specifications**

Radome Material ABS

Size

 Length
 8.19 in [208.03 mm]

 Width
 0.86 in [21.84 mm]

 Height
 0.51 in [12.95 mm]

 Weight
 0.05544 lbs [25.15 g]

# **Environmental Specifications**

**Temperature** 

Operating Range -20 to +65 deg C Storage Range -20 to +65 deg C

Compliance Certifications (see product page for current document)

### **Plotted and Other Data**

Notes:

3.3 GHz to 3.8 GHz Blade Style Antenna, Dipole, SMA Male Connector, 4.5 dBi Gain from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# **L-com CAD Drawing**

