

SMA Male to SMA Male Cable Using 402SS Series  
Coax with Heavy Duty Boot, 6.0 ft



**LCCA30001-FT6**

**Configuration**


- Connector 1: SMA Male
- Connector 2: SMA Male
- Cable Type: 402SS Series

**Features**

- Max Frequency 18 GHz
- Shielding Effectivity > 110dB
- 70% Phase Velocity
- Double Shielded
- FEP Jacket
- Wire Braid over Spiral Strip Shield
- Flexible Alternative to .141 Semi-Rigid
- Heavy Duty Heat Shrink Strain Relief Boot
- Precision Stainless Steel Connectors

**Applications**

- General Purpose
- Laboratory Use
- Flexible RF Interconnect
- Automated (ATE) Test Systems



**Description**

L-com's LCCA30001-FT6 is a SMA male to SMA male cable using 402SS series coax with heavy duty boot, 6.0 ft and ships same-day. The 402SS series coax of this SMA cable uses the PTFE dielectric with a VoP of 70%. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com SMA to SMA cable assembly has a male to male gender configuration with flexible 402SS series series coax and operates to 18 GHz. The double shield of this SMA cable is layered by silver plated copper braid over silver plated copper tape providing excellent shielding effectiveness greater than 110dB. L-com's Cable Assembly LCCA30001 is an SMA male to SMA male, 6.0 ft cable using 402SS Series coax with Heavy Duty Boot that ships same-day. L-com's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This L-com SMA to SMA cable assembly has a male to male gender configuration with 50 ohm flexible 402SS Series coax and operates to 18 GHz. Highly durable stainless-steel connectors and heavy-duty booting extend the life of this versatile flexible cable assembly. The double shield includes a silver plated copper braid over a silver plated copper spiral strip providing excellent shielding effectiveness greater than 110dB.

Custom versions of this cable assembly along with the rest of L-com's RF cable assemblies can be built and shipped same day. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for custom cable quotes.

Custom versions of this SMA male to SMA male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other

SMA Male to SMA Male Cable Using 402SS Series  
Coax with Heavy Duty Boot, 6.0 ft



**LCCA30001-FT6**

available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30001-FT6 L-com SMA Male to SMA Male Cable Using 402SS Series Coax with Heavy Duty Boot, 6.0 ft data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

**Electrical Specifications**

| Description             | Minimum | Typical      | Maximum | Units        |
|-------------------------|---------|--------------|---------|--------------|
| Frequency Range         | DC      |              | 18      | GHz          |
| VSWR                    |         |              | 1.4:1   |              |
| Velocity of Propagation |         | 70           |         | %            |
| RF Shielding            | 110     |              |         | dB           |
| Capacitance             |         | 29.4 [96.46] |         | pF/ft [pF/m] |

**Specifications by Frequency**

| Description           | F1    | F2    | F3   | F4    | F5 | Units |
|-----------------------|-------|-------|------|-------|----|-------|
| Frequency             | 3     | 5     | 10   | 18    |    | GHz   |
| Insertion Loss (Max.) | 1.484 | 1.935 | 2.89 | 4.095 |    | dB    |

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss is estimated as  $0.03 \cdot \sqrt{FGHz}$  dB per connector.

**Mechanical Specifications**

**Cable Assembly**

|          |                     |
|----------|---------------------|
| Length   | 72 in [182.88 cm]   |
| Diameter | 0.315 in [8 mm]     |
| Weight   | 0.27 lbs [122.47 g] |

**Cable**

|                                      |                            |
|--------------------------------------|----------------------------|
| Cable Type                           | 402SS Series               |
| Impedance                            | 50 Ohms                    |
| Inner Conductor Type                 | Stranded                   |
| Inner Conductor Material and Plating | Copper, Silver             |
| Dielectric Type                      | PTFE                       |
| Number of Shields                    | 2                          |
| Shield Layer 1                       | Silver Plated Copper Tape  |
| Shield Layer 2                       | Silver Plated Copper Braid |

SMA Male to SMA Male Cable Using 402SS Series  
Coax with Heavy Duty Boot, 6.0 ft



## LCCA30001-FT6

|                              |                    |
|------------------------------|--------------------|
| Jacket Material              | FEP, Blue          |
| Jacket Diameter              | 0.163 in [4.14 mm] |
| Repeated Minimum Bend Radius | 1 in [25.4 mm]     |

### Connectors

| Description                        | Connector 1                 | Connector 2                 |
|------------------------------------|-----------------------------|-----------------------------|
| Type                               | SMA Male                    | SMA Male                    |
| Specification                      | MIL-STD-348A                | MIL-STD-348A                |
| Impedance                          | 50 Ohms                     | 50 Ohms                     |
| Contact Material and Plating       | Brass, Gold                 | Brass, Gold                 |
| Contact Plating Specification      | 50 µin minimum              | 50 µin minimum              |
| Dielectric Type                    | PTFE                        | PTFE                        |
| Body Material and Plating          | Brass, Nickel               | Brass, Nickel               |
| Body Plating Specification         | 100 µin minimum             | 100 µin minimum             |
| Coupling Nut Material and Plating  | Brass, Nickel               | Brass, Nickel               |
| Coupling Nut Plating Specification | 100 µin minimum             | 100 µin minimum             |
| Hex Size                           | 5/16 inch                   | 5/16 inch                   |
| Torque                             | 12 in-lbs 1.36 Nm           | 12 in-lbs 1.36 Nm           |
| Boot Material                      | Heavy Duty Heat Shrink Boot | Heavy Duty Heat Shrink Boot |

### Environmental Specifications

#### Temperature

Operating Range -55 to +165 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

- Values at 25°C, sea level.

SMA Male to SMA Male Cable Using 402SS Series  
Coax with Heavy Duty Boot, 6.0 ft




**LCCA30001-FT6**

**How to Order**

Part Number Configuration:

**LCCA30001 - xx uu**



Example: LCCA30001-12 = 12 inches long cable  
LCCA30001-100cm = 100 cm long cable

SMA Male to SMA Male Cable Using 402SS Series Coax with Heavy Duty Boot, 6.0 ft from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# SMA Male to SMA Male Cable Using 402SS Series Coax with Heavy Duty Boot, 6.0 ft

## L-com CAD Drawing

| REVISIONS |                 |                    |
|-----------|-----------------|--------------------|
| REV.      | DESCRIPTION     | DATE               |
| A         | INITIAL RELEASE | 10/08/2019         |
|           |                 | APPROVED<br>SELLIS |

LENGTH MEASURED FROM CONTACT TO CONTACT

THIRD-ANGLE PROJECTION

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS

**TOLERANCES:**

|              |        |             |
|--------------|--------|-------------|
| .X = ±.2     | [.008] | FRACTIONS   |
| .XX = ±.02   | [.51]  | ±.102       |
| .XXX = ±.005 | [.15]  | ANGLES ± 1° |

OVERALL CABLE LENGTH (L) TOLERANCES:

|                      |                        |
|----------------------|------------------------|
| L ≤ 12               | [305] = +1 [25] / -0   |
| 12 [305] < L ≤ 60    | [1524] = +2 [51] / -0  |
| 60 [1524] < L ≤ 120  | [3048] = +4 [102] / -0 |
| 120 [3048] < L ≤ 300 | [7620] = +6 [152] / -0 |
| 300 [7620] < L       | = +5%L / -0            |

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

**an INFINITE brand**

50 High Street, West Mill, 3rd Floor, Suite #30  
North Andover, MA 01845 USA  
Phone: 1.800.341.5266 | 1.978.682.6936  
Fax: 1.978.669.9464  
www.L-com.com | e-mail: CustomerService@L-com.com

PART NUMBER  
**LCCA30001**

NOTES:

- CABLES 36" AND UNDER HAVE 1 LABEL CENTERED. CABLES OVER 36" HAVE 2 LABELS, ONE AT EACH END, 6.0" FROM THE FRONT OF THE CONNECTOR.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

SIZE | CAGE CODE | DRAWN BY | PART NUMBER

**A** | **43321** | **DFRISIELLO** | **LCCA30001**

T-RevC