



LCCA30192-FT4

Configuration

· Connector 1: N Male Right Angle

Connector 2: N MaleCable Type: LMR-400

Features

- Using Times Microwave Components
- Max Frequency 6 GHz
- Shielding Effectivity > 90 dB
- 85% Phase Velocity

Applications

- General Purpose
- · Laboratory Use
- Antenna Installations

- PE Jacket
- Low Insertion Loss
- · Bend Radius of 4 Inches
- Land Mobile Radio & Other Communication Systems
- · Cellular & Wi-Fi Systems



Description

L-com's LCCA30192-FT4 is a low loss N male right angle to N male cable assembly using LMR-400 coax, 4 FT with Times Microwave components and ships same-day. The LMR-400 coax of this N cable uses the PE (F) dielectric with a VoP of 85%, resulting in very low insertion loss compared to solid dielectrics. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com N to N cable assembly has a male to male gender configuration with flexible LMR-400 series coax and operates to 6 GHz. The double shield of this N cable is layered by tinned copper braid over aluminum tape providing shielding effectiveness greater than 90dB. This right angle N cable interface on the LMR-400 coax allows for easier connections in tight spaces. *LMRTM is a trademark of Times Microwave Systems.

Custom versions of this N male to N male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30192-FT4 L-com Low Loss N Male Right Angle to N Male Cable Assembly using LMR-400 Coax, 4 FT with Times Microwave Components data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.





LCCA30192-FT4

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		85		%
RF Shielding	90			dB
Group Delay		1.2 [3.94]		ns/ft [ns/m]
Capacitance		23.9 [78.41]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor	•	1.39 [4.56]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conducto	r	1.65 [5.41]		Ohms/1000ft [Ohms/Km]
Jacket Spark			8,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	6	GHz
Insertion Loss (Typ.)	0.38	0.41	0.46	0.57	0.74	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB for the straight connector and 0.2 dB for the right angle connector.

Mechanical Specifications

Cable Assembly

 Length
 48 in [121.92 cm]

 Diameter
 0.8 in [20.32 mm]

Cable

Cable TypeLMR-400Impedance50 OhmsInner Conductor TypeSolid

Inner Conductor Material and Plating Copper Clad Aluminum Dielectric Type PE (F)

Number of Shields 2
Shield Laver 1

Shield Layer 1 Aluminum Tape
Shield Layer 2 Tinned Copper Braid





LCCA30192-FT4

Jacket Material Jacket Diameter

One Time Minimum Bend Radius Repeated Minimum Bend Radius Bending Moment Flat Plate Crush Tensile Strength PE, Black

0.405 in [10.29 mm]

1 in [25.4 mm] 4 in [101.6 mm] 0.5 lbs-ft [0.68 N-m] 40 lbs/in [0.71 Kg/mm] 160 lbs [72.57 Kg]

Connectors

Description	Connector 1	Connector 2	
Туре	N Male Right Angle	N Male	
Impedance	50 Ohms	50 Ohms	
Mating Cycles	500		
Contact Material and Plating	Brass, Gold	Brass, Gold	
Contact Plating Specification		50 μ in. minimum	
Dielectric Type	Teflon	PTFE	
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal	
Body Plating Specification		150 μ in. minimum	
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal	
Coupling Nut Plating Specification		150 μ in. minimum	
Hex Size	13/16 inch	13/16 inch	
Torque	30 in-lbs 3.39 Nm		

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C Storage Range -70 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data


Notes:





LCCA30192-FT4

How to Order



Example: LCCA30192-12 = 12 inches long cable

LCCA30192-100cm = 100 cm long cable

Low Loss N Male Right Angle to N Male Cable Assembly using LMR-400 Coax, 4 FT with Times Microwave Components from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

