

## Low Loss N Male to SMA Male Cable Assembly using LMR-200-UF Coax With Times Microwave Components with HeatShrink, LF Solder



### LCCA9885

#### Configuration

- Connector 1: N Male
- Connector 2: SMA Male
- Cable Type: LMR-200-UF
- Coax Flex Type: Flexible

#### Description

L-com's LCCA9885 is a low loss N male to SMA male cable assembly using LMR-200-UF coax with Times Microwave components with heatshrink, LF solder and ships same-day. The LMR-200-UF coax of this N cable uses the PE (F) dielectric with a VoP of 83%, resulting in very low insertion loss compared to solid dielectrics. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com N to SMA cable assembly has a male to male gender configuration with flexible LMR-200-UF series coax and operates to 5.8 GHz. The double shield of this N cable is layered by tinned copper braid over aluminum tape providing shielding effectiveness greater than 90dB.

Custom versions of this N male to N male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA9885 L-com Low Loss N Male to SMA Male Cable Assembly using LMR-200-UF Coax With Times Microwave Components with HeatShrink, LF Solder data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.5:1	
Velocity of Propagation		83		%
RF Shielding	90			dB
Group Delay		1.22 [4]		ns/ft [ns/m]
Capacitance		24.5 [80.38]		pF/ft [pF/m]
Inductance		0.061 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		7.5 [24.61]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		4.9 [16.08]		Ohms/1000ft [Ohms/Km]
Dielectric Withstanding Voltage (DC)			1,000	Vdc
Jacket Spark			3,000	Vrms
Input Power (Peak)			2.5	KWatts

#### Specifications by Frequency

## Low Loss N Male to SMA Male Cable Assembly using LMR-200-UF Coax With Times Microwave Components with HeatShrink, LF Solder



### LCCA9885

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	250	500	1000	2500	5800	MHz	
LCCA9885	Custom Lengths Available	Insertion Loss (Typ.)	0.061	0.087	0.125	0.202	0.316	dB/ft	
			0.21	0.29	0.42	0.67	1.04	dB/m	
LCCA9885-12	12 inch	Insertion Loss (Typ.)	0.22	0.26	0.33	0.47	0.66	dB	0.142
LCCA9885-24	24 inch	Insertion Loss (Typ.)	0.28	0.35	0.45	0.67	0.98	dB	0.165
LCCA9885-36	36 inch	Insertion Loss (Typ.)	0.34	0.44	0.58	0.87	1.29	dB	0.187
LCCA9885-60	60 inch	Insertion Loss (Typ.)	0.46	0.61	0.83	1.27	1.93	dB	0.231
LCCA9885-300	300 inch	Insertion Loss (Typ.)	1.68	2.35	3.33	5.31	8.25	dB	0.672

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB  
 Loss due to Connector 2:  $0.1 \cdot \sqrt{f(\text{GHz})}$  dB  
 Base Weight: 0.142 pounds  
 Additional Weight per Inch: 0.00184 pounds

Electrical Specification Notes:  
 Values at 25°C, sea level.

### Mechanical Specifications

#### Cable Assembly

Width/Diameter: 0.5 in [12.7 mm]  
 Weight: 0.142 lbs [64.41 g]

#### Cable

Cable Type: LMR-200-UF  
 Impedance: 50 Ohms  
 Inner Conductor Type: Stranded  
 Inner Conductor Material and Plating: Copper  
 Dielectric Type: PE (F)  
 Number of Shields: 2  
 Shield Layer 1: Aluminum Tape  
 Shield Layer 2: Tinned Copper Braid  
 Jacket Material: TPE  
 Jacket Diameter: 0.195 in [4.95 mm]  
 One Time Minimum Bend Radius: 0.5 in [12.7 mm]  
 Repeated Minimum Bend Radius: 2 in [50.8 mm]  
 Bending Moment: 0.1 lbs-ft [0.14 N-m]

Low Loss N Male to SMA Male Cable Assembly  
using LMR-200-UF Coax With Times Microwave  
Components with HeatShrink, LF Solder



## LCCA9885

### Connectors

Description	Connector 1	Connector 2
Type	N Male	SMA Male
Specification	MIL-STD-348	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Specification		ASTM B488
Dielectric Type	PTFE	Teflon
Body Material and Plating	Brass, Tri-Metal	Passivated Stainless Steel
Body Plating Specification		SAE-AMS-2700
Coupling Nut Material and Plating	Brass, Tri-Metal	Passivated Stainless Steel
Coupling Nut Plating Specification		SAE-AMS-2700
Hex Size	13/16 Inch	5/16 Inch

### Environmental Specifications

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

Values at 25°C, sea level.

## Low Loss N Male to SMA Male Cable Assembly using LMR-200-UF Coax With Times Microwave Components with HeatShrink, LF Solder



### LCCA9885

#### Typical Performance Data

#### How to Order

Part Number Configuration:

**LCCA9885**

**- xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: LCCA9885-12 = 12 inches long cable  
LCCA9885-100cm = 100 cm long cable

Low Loss N Male to SMA Male Cable Assembly using LMR-200-UF Coax With Times Microwave Components with HeatShrink, LF Solder from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/n-male-sma-male-cable-assembly-invalid-lcca9885-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

LCCA9885 CAD Drawing

Low Loss N Male to SMA Male Cable Assembly using LMR-200-UF Coax With Times Microwave Components with HeatShrink, LF Solder

