


Hand Formable Test Probe SMA Male to Trimmed Lead Cable Assembly using LC047TB Coax, Gold Plated Brass Body, 9 IN



LCCA30713-9IN

Configuration


- Connector 1: SMA Male
- Connector 2: Trimmed Lead
- Cable Type: LC047TB

Features

- 100% RF Tested prior to final trim
- 1.4 Max VSWR to 20 GHz
- 100% High Pot Tested to 500V
- 0.047 Diameter Formable coax
- Individually packed in protective tube

Applications

- Used as an RF Test Probe to 20 GHz
- RF PCB Board Measurements
- Signal Injection



Description

L-com's LCCA30713-9IN is a Test Probe SMA Male to Trimmed Lead Cable Assembly using LC047TB Coax, 0.75 FT and ships same-day. L-com's formable cable assemblies provide a convenient alternative to their semi-rigid versions, as they offer similar electrical performance but can be bent to desired shape without the use of special tools. Our L-com SMA to pre-trimmed cable assembly has a Male to sexless gender configuration with formable LC047TB series coax and operates to 20 GHz. The tinned copper braid outer conductor can be easily formed by hand and has an overall diameter of 0.047 inches.

The Test Probe SMA Male to Trimmed Lead Cable Assembly using LC047TB Coax, 0.75 FT is a convenient test probe designed to be directly soldered to an exposed microstrip trace to inject a signal or to measure a signal of interest. Each LCCA30713-9IN cable assembly is built with a connector on both ends to verify the electrical performance of 20 GHz with a maximum VSWR of 1.4:1. The cable is then trimmed and placed in a reusable protective tube. These test probes are available with a flush cut or a pre-trimmed cable lead.

Custom versions of this SMA Male to trimmed lead cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30713-9IN L-com Test Probe SMA Male to Trimmed Lead Cable Assembly using LC047TB Coax, 0.75 FT data sheet PDF include details of the RF product specifications, CAD drawing(s) and dimensions below.

Hand Formable Test Probe SMA Male to Trimmed Lead Cable
Assembly using LC047TB Coax, Gold Plated Brass Body, 9 IN



LCCA30713-9IN

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		20	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
Capacitance		32 [104.99]		pF/ft [pF/m]
DC Resistance Inner Conductor		207 [679.13]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		8 [26.25]		Ohms/1000ft [Ohms/Km]

Mechanical Specifications


Cable Assembly

Length 9 in [228.6 mm]

Cable

Cable Type LC047TB
 Impedance 50 Ohms
 Inner Conductor Type Solid
 Inner Conductor Material and Plating Copper Clad Steel, Silver
 Dielectric Type PTFE
 Number of Shields 1
 Outer Conductor Material and Plating Tinned Copper Braid

Hand Formable Test Probe SMA Male to Trimmed Lead Cable
Assembly using LC047TB Coax, Gold Plated Brass Body, 9 IN



LCCA30713-9IN

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	Trimmed Lead
Impedance	50 Ohms	
Mating Cycles	500	
Contact Material and Plating	Beryllium Copper, Gold over Nickel	
Contact Plating Specification	MIL-G-45204	
Dielectric Type	PTFE	
Body Material and Plating	Brass, Gold	
Body Plating Specification	MIL-G-45204	
Coupling Nut Material and Plating	Passivated Stainless Steel	
Coupling Nut Plating Specification	ASTM-A380	
Hex Size	5/16 inch	
Torque	8 in-lbs 0.9 Nm	

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Hand Formable Test Probe SMA Male to Trimmed Lead Cable Assembly using LC047TB Coax, Gold Plated Brass Body, 9 IN




LCCA30713-9IN

How to Order

Part Number Configuration:

LCCA30713 - xx uu



Example: LCCA30713-12 = 12 inches long cable
LCCA30713-100cm = 100 cm long cable

Hand Formable Test Probe SMA Male to Trimmed Lead Cable Assembly using LC047TB Coax, Gold Plated Brass Body, 9 IN from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Hand Formable Test Probe SMA Male to Trimmed Lead Cable Assembly using LC047TB Coax, Gold Plated Brass Body, 9 IN

L-com CAD Drawing

