

Low Loss N Female to SMA Male Cable Assembly using LMR-400-UF Coax With Times Microwave Components with HeatShrink



LCCA9954

Configuration

- Connector 1: N Female
- Connector 2: SMA Male
- Cable Type: LMR-400-UF
- Coax Flex Type: Flexible

Description

L-com's LCCA9954 is a low loss N female to SMA male cable assembly using LMR-400-UF coax with Times Microwave components with heatshrink and ships same-day. The LMR-400-UF coax of this N cable uses the PE (F) dielectric with a VoP of 85%, resulting in very low insertion loss compared to solid dielectrics. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com N to SMA cable assembly has a female to male gender configuration with flexible LMR-400-UF series coax and operates to 5.8 GHz. The double shield of this N cable is layered by tinned copper braid over aluminum tape providing shielding effectiveness greater than 90dB.

Custom versions of this N female to N male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA9954 L-com Low Loss N Female to SMA Male Cable Assembly using LMR-400-UF Coax With Times Microwave Components with HeatShrink data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|--------------------------------------|---------|--------------|---------|-----------------------|
| Frequency Range | DC | | 5.8 | GHz |
| VSWR | | | 1.5:1 | |
| Velocity of Propagation | | 85 | | % |
| RF Shielding | 90 | | | dB |
| Group Delay | | 1.2 [3.94] | | ns/ft [ns/m] |
| Capacitance | | 23.9 [78.41] | | pF/ft [pF/m] |
| Inductance | | 0.06 [0.2] | | uH/ft [uH/m] |
| DC Resistance Inner Conductor | | 1.07 [3.51] | | Ohms/1000ft [Ohms/Km] |
| DC Resistance Outer Conductor | | 1.65 [5.41] | | Ohms/1000ft [Ohms/Km] |
| Dielectric Withstanding Voltage (DC) | | | 2,500 | Vdc |
| Jacket Spark | | | 8,000 | Vrms |
| Input Power (Peak) | | | 16 | KWatts |

Specifications by Frequency

Low Loss N Female to SMA Male Cable Assembly using LMR-400-UF Coax With Times Microwave Components with HeatShrink



LCCA9954

| Part Number | Length | Description | F1 | F2 | F3 | F4 | F5 | Units | Weight (lbs) |
|---------------|--------------------------|-----------------------|-------|-------|-------|-------|------|-------|--------------|
| | | Frequency | 250 | 500 | 1000 | 2500 | 5800 | MHz | |
| LCCA9954 | Custom Lengths Available | Insertion Loss (Typ.) | 0.023 | 0.034 | 0.049 | 0.081 | 0.13 | dB/ft | |
| | | | 0.08 | 0.12 | 0.17 | 0.27 | 0.43 | dB/m | |
| LCCA9954-FT1 | 12 inch | Insertion Loss (Typ.) | 0.23 | 0.24 | 0.25 | 0.29 | 0.33 | dB | 0.226 |
| LCCA9954-FT2 | 24 inch | Insertion Loss (Typ.) | 0.25 | 0.27 | 0.3 | 0.37 | 0.46 | dB | 0.313 |
| LCCA9954-FT3 | 36 inch | Insertion Loss (Typ.) | 0.27 | 0.31 | 0.35 | 0.45 | 0.59 | dB | 0.4 |
| LCCA9954-FT5 | 60 inch | Insertion Loss (Typ.) | 0.32 | 0.37 | 0.45 | 0.61 | 0.85 | dB | 0.574 |
| LCCA9954-FT25 | 300 inch | Insertion Loss (Typ.) | 0.78 | 1.05 | 1.43 | 2.23 | 3.45 | dB | 2.314 |

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

| | |
|-----------------------------|----------------|
| Loss due to Connector 1: | 0.1 dB |
| Loss due to Connector 2: | 0.1 dB |
| Base Weight: | 0.226 pounds |
| Additional Weight per Inch: | 0.00725 pounds |

Mechanical Specifications

Cable Assembly

| | |
|----------------|----------------------|
| Width/Diameter | 0.5 in [12.7 mm] |
| Weight | 0.226 lbs [102.51 g] |

Cable

| | |
|--------------------------------------|------------------------|
| Cable Type | LMR-400-UF |
| Inner Conductor Type | Stranded |
| Inner Conductor Material and Plating | Copper |
| Dielectric Type | PE (F) |
| Number of Shields | 2 |
| Shield Layer 1 | Aluminum Tape |
| Shield Layer 2 | Tinned Copper Braid |
| Jacket Material | TPE |
| Jacket Diameter | 0.405 in [10.29 mm] |
| One Time Minimum Bend Radius | 1 in [25.4 mm] |
| Repeated Minimum Bend Radius | 4 in [101.6 mm] |
| Bending Moment | 0.38 lbs-ft [0.52 N-m] |
| Flat Plate Crush | 20 lbs/in [0.36 Kg/mm] |
| Tensile Strength | 160 lbs [72.57 Kg] |

Low Loss N Female to SMA Male Cable Assembly using LMR-400-UF Coax With Times Microwave Components with HeatShrink



LCCA9954

Connectors

| Description | Connector 1 | Connector 2 |
|-----------------------------------|------------------|------------------|
| Type | N Female | SMA Male |
| Specification | MIL-STD-348 | |
| Configuration | Straight | Straight |
| Contact Material and Plating | Copper, Gold | Brass, Gold |
| Contact Plating Specification | | 50µin. minimum |
| Dielectric Type | PTFE | Teflon |
| Body Material and Plating | Brass, Tri-Metal | Brass, Tri-Metal |
| Coupling Nut Material and Plating | Brass, Tri-Metal | Brass, Tri-Metal |

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Values at 25°C, sea level.

Low Loss N Female to SMA Male Cable Assembly using LMR-400-UF Coax With Times Microwave Components with HeatShrink



LCCA9954

Typical Performance Data

How to Order

Part Number Configuration:

LCCA9954

- xx

uu

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: LCCA9954-12 = 12 inches long cable
LCCA9954-100cm = 100 cm long cable

Low Loss N Female to SMA Male Cable Assembly using LMR-400-UF Coax With Times Microwave Components with HeatShrink from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/n-female-sma-male-cable-assembly-invalid-lcca9954-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Low Loss N Female to SMA Male Cable Assembly using LMR-400-UF Coax With Times Microwave Components with HeatShrink

