

2 Watt RF Load DC to 12 GHz With TNC Female Brass Body



LCTR1148

Features

- DC to 12 GHz Frequency Range
- 50 Ohm Impedance
- TNC Female Coaxial Interface
- Max VSWR 1.2:1
- Max Power 2 Watts (CW)

Applications

- WIFI 6E
- 5G Cellular bands
- SatCom
- Radar Systems
- Test and Measurement
- Commercial and Military Communication

Description

L-com's LCTR1148 is an RF termination (also called RF load or dummy load) that operates from DC to 12 GHz and handles up to 2 Watt (CW). Our TNC termination / load has a female gender. LCTR1148 TNC load termination offers 1.2:1 max VSWR.

RF load / terminations are indispensable components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can potentially damage the device or reduce the signal integrity. By using a terminator on an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, circulators, and switches. They are also widely used in measurement systems to ensure accurate results. L-com offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watt (CW).

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12	GHz
Impedance		50		Ohms
VSWR			1.2:1	
Input Power (CW)			2	Watts
Derated linearly to 1W at +165°C				
Dielectric Withstanding Voltage (DC)			1,500	Vdc
Operating Voltage (DC)			500	Vdc

Mechanical Specifications

Size

Length	0.902 in [22.91 mm]
Width	0.433 in [11 mm]
Height	0.433 in [11 mm]
Weight	0.025 lbs [11.34 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[2 Watt RF Load DC to 12 GHz With TNC Female Brass Body LCTR1148](#)

2 Watt RF Load DC to 12 GHz With TNC Female Brass Body



LCTR1148

Configuration

Connector

TNC Female

Material Specifications

Description	Material	Plating
Connector 1 Contact	Phosphor Bronze	Gold
Insulation	Teflon	
Body	Brass	Copper-Tin-Zinc Alloy

Environmental Specifications

Temperature

Operating Range

-55 to +165 deg C

Humidity

MIL-STD-202, Method 106

Thermal Shock

MIL-STD-202, Method 107, Condition B

Salt Spray

MIL-STD-202, Method 101, Condition B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

2 Watt RF Load DC to 12 GHz With TNC Female Brass Body from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 2 Watt RF Load DC to 12 GHz With TNC Female Brass Body LCTR1148

URL: <https://www.l-com.com/2-watt-rf-load-dc-12-ghz-tnc-female-brass-body-lctr1148-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

2 Watt RF Load DC to 12 GHz With TNC Female Brass Body

L-com CAD Drawing

