

Low Loss Flexible LMR-LW240 Light Weight Coax Cable  
Double Shielded with Black PE Jacket, By the Foot



## LMR-LW240-LC-FT

### Configuration

- Low Loss, Outdoor Flexible Cable
- 2 Shield(s)

### Features

- PE Jacket
- Max Operating Temperature +85°C
- Min Install Bend Radius of 0.75 inches
- Phase Velocity 83% VoP
- Max Operating Frequency of 8 GHz
- Light Weight Coax

### Applications

- Antenna Installations
- RF Test Systems
- General Purpose RF Interconnect
- Laboratory Applications

### Description

LMR-LW240-LC coax cable from L-com is only one of a large number of radio frequency coaxial cable types specifically stocked to be ready for quick shipment. L-com LMR-LW240-LC coax cable is manufactured in a flexible design and has a 50 Ohm impedance. This low loss flexible 50 Ohm coax cable LMR-LW240-LC is constructed with a 0.240 inch diameter and Black PE jacket.

LMR-LW240-LC flexible 50 Ohm coax cable with PVC jacket is rated for a 8 GHz maximum operating frequency. This 50 Ohm 0.240 inch diameter and low loss flexible coax cable is built with a double shield count and RF shielding of 90 dB. L-com LMR-LW240-LC coax is constructed with Foam PE dielectric and a maximum operating temperature of +85 degrees C. Times Microwave LMR-LW240-LC coax cable specs for this wire properties can be found on its RF coax cable LMR-LW240-LC datasheet.

LMR-LW240-LC cable is part of more than one million RF, microwave parts in stock at L-com. This Times Microwave low loss LMR-LW240-LC coax cable is ready to buy and can be shipped worldwide. L-com also maintains a wide selection of other radio frequency coaxial cable types that ship same-day from our warehouse as with the rest of our other RF/microwave components.

\* LMR™ is a trademark of Times Microwave Systems.

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		8	GHz
Impedance		50		Ohms
Velocity of Propagation		83		%
Time Delay		1.21 [3.97]		ns/ft [ns/m]
Shielding Effectiveness	90			dB
Dielectric Withstanding Voltage (DC)			1,500	Vdc
Jacket Spark			5,000	Vrms
Nominal Capacitance		24.2 [79.4]		pF/ft [pF/m]

Low Loss Flexible LMR-LW240 Light Weight Coax Cable  
Double Shielded with Black PE Jacket, By the Foot



**LMR-LW240-LC-FT**

Nominal Inductance	0.06 [0.2]	uH/ft [uH/m]
Input Power (Peak)	5.6	kWatts

**Performance by Frequency Band**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.05	0.15	0.45	0.9	1.5	GHz
Attenuation, Typ	1.7	3	3.7	5.3	7.6	dB/100ft
	5.58	9.84	12.14	17.39	24.93	dB/100m
Input Power (CW), Max	1,150	660	540	380	260	Watts

Description	F6	F7	F8	F9	F10	Units
Frequency	1.8	2	2.5	5.8	8	GHz
Attenuation, Typ	9.9	10.9	11.5	12.9	20.4	dB/100ft
	32.48	35.76	37.73	42.32	66.93	dB/100m
Input Power (CW), Max	200	180	170	150	100	Watts

**Mechanical Specifications**

Diameter	0.24 in 6.1 mm
Weight	0.026 lbs/ft [0.04 kg/m]
Min. Bend Radius (Installation)	0.75 in [19.05 mm]
Min. Bend Radius (Repeated)	2.5 in [63.5 mm]
Bending Moment	0.25 lbs-ft [0.34 N-m]
Tensile Strength	80 lbs [36.29 kg]
Flat Plate Crush	20 lbs/in [0.36 kg/mm]

**Construction Specifications**

Description	Material and Plating	Diameter
Inner Conductor	Copper , 1 Strands Strand(s)	0.056in 1.42mm
Conductor Type	Solid	
Dielectric	Foam PE	0.15in 3.81mm
First Shield	Aluminum Tape	
Second Shield	Aluminium	
Jacket	PE, Black	0.24in 6.1mm

Low Loss Flexible LMR-LW240 Light Weight Coax Cable  
Double Shielded with Black PE Jacket, By the Foot



## LMR-LW240-LC-FT

### Environmental Specifications

#### Temperature


Operating Range	-40deg C to +85deg C
Installation Range	-40deg C to +85deg C
Storage Range	-70deg C to +85deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Low Loss Flexible LMR-LW240 Light Weight Coax Cable Double Shielded with Black PE Jacket, By the Foot from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS		<div><div><div>L-com™</div><div>an INFINITE® brand</div></div><div>50 High Street, West Mill, 3rd Floor, Suite #30 North Andover, MA 01845 USA. Phone: 1.800.341.5266   1.978.682.6936 Fax: 1.978.689.9484 Website: <a href="http://www.L-com.com">www.L-com.com</a> E-mail: <a href="mailto:CustomerService@L-com.com">CustomerService@L-com.com</a></div></div>		THIRD-ANGLE PROJECTION <div><div></div><div>THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED.</div></div> <div><div>SHEET1</div><div>OF1</div></div> <div>SCALEN/A</div>			
TOLERANCES: <div><div><div><div><math>X = \pm .2</math></div><div>[5.08]</div></div><div>FRACTIONS</div><div><math>XX = \pm .02</math></div><div>[.51]</div></div><div><math>XXX = \pm .005</math></div><div>[.13]</div></div> <div>TOLERANCES <math>\pm .1^\circ</math></div> <div>CABLE LENGTH (L) ANGLES: <div><div><div><math>L \leq 12</math></div><div>[305]</div><div>= +1</div><div>[25] / -0</div></div><div><div><math>12</math></div><div>[305]</div><div>&lt; L <math>\leq 60</math></div><div>[1524]</div><div>= +2</div><div>[51] / -0</div></div><div><div><math>60</math></div><div>[1524]</div><div>&lt; L <math>\leq 120</math></div><div>[3048]</div><div>= +4</div><div>[102] / -0</div></div><div><div><math>120</math></div><div>[3048]</div><div>&lt; L <math>\leq 300</math></div><div>[7620]</div><div>= +6</div><div>[152] / -0</div></div><div><div><math>300</math></div><div>[7620]</div><div>&lt; L <math>\leq +5\%</math></div><div>/ -0</div></div></div></div>		SIZEA		CAGE CODE43321	DRAWN BYDZINN	ITEM NO.LMR-LW240-LC-FT	REVA
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY							

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.