

MPO w/ pins to FLC Fan-out, 8 fiber round, OM5 50/125µm Multimode, LSZH Jacket, Lime Green, 5 meter



## MPM8OM5-FLCZ-5

### Features

- Fan-out connectors unclipped for custom Polarity requirements
- MPO fan-out to flexible boot LC connectors for server-to-switch and other link aggregation
- Used to connect equipment that utilizes MPO style connectors and OM5 50/125µm Multimode cabling for aggregation of links
- LSZH (Low Smoke Zero Halogen) jacket gives off very little smoke and does not produce toxic halogen based gasses

### Applications

- Link Aggregation
- Data Centers/Enterprise Networking
- Ethernet
- Server connectivity

### Description

The MPM8OM5-FLCZ-5 from L-com is a fan-out cable assembly that comes with a MPO (w/ pins) male to LC male connector configuration. This fiber optic cable with 8 fibers features an LSZH-rated jacket and has a cable diameter of 3 mm. Our fan-out cable is suitable for applications such as data centers, Ethernet, link aggregation, and server connectivity. This lime green fiber optic cable assembly is available in a length of 5 meters and can withstand temperatures ranging from -40 to 75 degrees C.

Our MPO (w/ pins) to LC cable comes with a multimode OM5 fiber and has a fiber diameter of 50/125 µm. L-com's fan-out cable assembly is ideal for making connections within rack mounted or wall mounted fiber enclosures. Our fiber optic cable assembly can be customized in different lengths to fit specific installation needs, ensuring efficient network management in high-density setups without compromising delivery time or quality. Additional dimensions, specifications, and CAD drawings for this MPM8OM5-FLCZ-5 fan-out cable can be found on its downloadable PDF datasheet.

L-com has one of the largest in-stock selections of fiber optic cable assemblies for international and domestic orders. Make your online purchase right now to take advantage of our same-business-day shipping. We are committed to delivering excellent service to support our customers in maintaining the continuity and reliability of their networks. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal multimode OM5 fan-out cable for your requirements.

### Configuration

|                     |                  |
|---------------------|------------------|
| Function            | Fan-out          |
| Cable Type          | Base-8 Multimode |
| Mode                | Multimode        |
| Mode Class          | OM5              |
| Fiber Diameter      | 50/125 µm        |
| Connection 1 Type   | MPO (w/ pins)    |
| Connection 1 Gender | Male             |
| Connection 1 Polish | UPC              |
| Connection 2 Type   | LC               |
| Connection 2 Polish | PC               |
| Cable Color         | Lime Green       |

### Optical Specifications

| Description                  | Minimum | Typical | Maximum | Units |
|------------------------------|---------|---------|---------|-------|
| Return Loss - MPO            | 20      |         |         | dB    |
| Insertion Loss - MPO         |         |         | 0.75    | dB    |
| Return Loss - LC, ST, SC, FC | 20      |         |         | dB    |

MPO w/ pins to FLC Fan-out, 8 fiber round, OM5 50/125µm Multimode, LSZH Jacket, Lime Green, 5 meter



## MPM8OM5-FLCZ-5

### Optical Specifications

| Description                     | Minimum | Typical | Maximum | Units |
|---------------------------------|---------|---------|---------|-------|
| Insertion Loss - LC, ST, SC, FC |         |         | 0.3     | dB    |

### Mechanical Specifications

#### Cable Assembly

|                |                 |
|----------------|-----------------|
| Length         | 5 m [196.85 in] |
| Width/Diameter | 3 mm            |

#### Cable

|  |         |
|--|---------|
| Cable Type                                 | Fan-out |
| Polarity                                   | Neutral |
| Breakout Diameter                          | 2 mm    |
| Static Bend Radius                         | 30 mm   |
| Dynamic Bend Radius                        | 60 mm   |
| Max Crush Resistance, Short Term (N/100mm) | 500     |
| Max Crush Resistance, Long Term (N/100mm)  | 100     |

### Connectors

| Description      | Connector 1        | Connector 2 |
|------------------|--------------------|-------------|
| Type             | MPO (w/ pins) Male | LC          |
| Configuration    | Straight           |             |
| Connector Polish | UPC                | PC          |

### Environmental Specifications

|                                |                  |
|--------------------------------|------------------|
| Operating Range Temperature    | -40 to +75 deg C |
| Ingress Protection (IP) Rating | Non-Rated        |

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

MPO w/ pins to FLC Fan-out, 8 fiber round, OM5 50/125µm Multimode, LSZH Jacket, Lime Green, 5 meter



## MPM8OM5-FLCZ-5

### Typical Performance Data

### How to Order

Part Number Configuration:

**MPM8OM5-FLCZ**

**-XX**

**UU**

Unit of Measure:

F = Feet

<blank> = Meters

Lengths

Base Number

Example: MPM8OM5-FLCZ-12 = 12 meters long cable  
MPM8OM5-FLCZ-10F = 10 feet long cable


MPO w/ pins to FLC Fan-out, 8 fiber round, OM5 50/125µm Multimode, LSZH Jacket, Lime Green, 5 meter from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/fiber-optic-mpo-w-pins-to-flc-fan-out-8-fiber-roundom5-50-125um-multimode-lszh-jacket-lime-green-5-meter>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# MPM8OM5-FLCZ-5 CAD Drawing

MPO w/ pins to FLC Fan-out, 8 fiber round, OM5 50/125µm Multimode, LSZH Jacket, Lime Green, 5 meter



|   |  |   |
|---|--|---|
| <p>UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS IN INCHES, DIMENSIONS IN [ ] ARE MILLIMETERS</p> <p>TOLERANCES:</p> <p>X = ±.2 [5]      FRACTIONS ± 1/32</p> <p>.XX = ±.02 [0.5]      ANGLES ± 1°</p> <p>.XXX = ±.005 [0.13]</p> <p>CABLE LENGTH TOLERANCES:</p> <p>512 (205) = ±1 (25) /-0</p> <p>&gt;12 (305) ≤ 60 (1524) = ±2 (51) /-0</p> <p>&gt;60 (1524) ≤ 300 (7620) = ±6 (152) /-0</p> <p>&gt;300 (7620) = ±8 (203) /-0</p> | <p><b>L-com</b><br/>an INFINITE brand<br/>Website: <a href="http://www.L-com.com">www.L-com.com</a><br/>Phone: 1.800.341.5266   1.978.682.6936</p> | <p>INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5</p> <p>SCALE NONE</p> <p>SHEET 1 OF 1</p> |
| <p>DESCRIPTION<br/>MPO W/ PINS TO FLC FAN-OUT, 8 FIBER ROUND, OM5 50/125µm MULTIMODE, LSZH JACKET, LIME GREEN</p>   |  |   |
| <p>SIZE A</p>   | <p>CAGE CODE 43321</p>   | <p>REV B</p>  |
| <p>DRAWN BY DFRISIELLO</p>  | <p>ITEM NO. MPM8OM5-FLCZ</p>   | <p>REV B</p>  |

- NOTES:
- ALL CONNECTORS SUPPLIED WITH A DUST CAP INSTALLED (NOT SHOWN).
  - CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.
  - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IAW L-COM SPECIFICATION PS-0031.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

LC DS Rev-04 Adda