

# 18x16x8 Inch Vented Weatherproof Enclosure with Mounting Rail for DIN3 Rails and DIN Modules - Model: NB181608-00VDR

# **Applications and Features**


#### Features:

- Molded Fiberglass Reinforced Polyester (FRP) industrial Enclosure
- Stainless steel quick release latches with padlock hasps
- NEMA Type 3R, 3RX / IP24 rated
- Fully gasketed raised Vented lid & integral mounting flange
- Includes Mounting Rails for DIN3 Rails and DIN modules in the Enclosure

## **Applications:**



- DIN Rail mountable Modular System
- Indoor and outdoor installations and Remote Wireless LAN WiFi equipment
- Rapid Deployment Installations
- Corrosive environments & hotspot applications
- Protection of equipment from theft or damage





# **Product Description**

#### Start with the Box...

The box is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded fiberglass reinforced polyester, it is well suited for high temperature or corrosive environments. The mounting flange allows it to be wall mounted as well as on a flat surface. The raised lid features a stainless steel continuous hinge and stainless steel quick release latches with padlock hasps. The raised lid is fully gasketed. The enclosure material is UV stabilized and comes in machine tool gray.

## **Mounting Rails**

The aluminum mounting rails installed within the NB141608-00VDR provides provisions to mount DIN3 Rails for installing a number of off-the-shelf DIN Modules and systems. The HGX-PMT13 Mounting package allows the populated enclosure to be mounted on poles, securely, in and around your site. The flexibility of DIN rail mounting system and the large selection of modules available offer any number of application solutions indoors and out, even in rainy environments. The NEMA Type 3R, 3RX / IP24 provides a vented, weatherproof environment, to safely house the control, routing and power systems being designed with the DIN Modules. The DIN Rails can be adapted to hold other systems and components to accommodate their placement in the enclosure. The enclosure features holes for two N-Bulkhead connectors or Lightning Protectors, a grounding lug, and a cable conduit connector to accept power or system feeds into the enclosure.

## **Vented Cover**

The NB181608-00VDR features a vented lid with removable filters and vent covers on the outside of the enclosure.

## **Specifications**

Enclosure Material	Fiberglass Reinforced Polyester
Enclosure Color	Machine Tool Gray
Mounting Rails Material	.125 " (.3 cm) or 8 Gauge Thick Anodized Aluminum
Mounting Rails Dimensions	12.7 x 10.8 inches (32.2 x 27.4 cm)
Weight	19.0 lbs (8.6 kg)
Outside Dimensions (max)	19.3 x 17.3 x 9.6 inches (49.1 x 43.9 x 24.4 cm)
Inside Dimensions	17.7 x 15.7 x 8.5 inches (45.0 x 39.9 x 21.6 cm)
Flame Rating	UL 94-5V
Cable Feed	1/2" Cable Conduit Connector
RoHS Compliant	Yes
Ratings	NEMA 3R, 3RX / IP24



# **Enclosure Dimensions**

