


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/10/2023	HBAKKE	AGANWANI



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 <p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p> <p>CATEGORY</p> <p>COAXIAL</p>	
OVERALL CABLE LENGTH TOLERANCE:	DRAWN BY HBAKKE	05/10/2023		
≤ 12 [305] = +1 [25] / -0	CHECKED BY DMAY	05/10/2023		
> 12 [305] ≤ 60 [1524] = +2 [51] / -0	APPROVED BY KLEITLIN	05/10/2023		
> 60 [1524] ≤ 120 [3048] = +4 [102] / -0	PRODUCT DESCRIPTION			
> 120 [3048] ≤ 300 [7620] = +6 [152] / -0	SMA Male to BNC Male Cable Using RG316 Coax, LF Solder, RoHS			
> 300 [7620] = +5% / -0				
ALL OTHER DIMENSIONAL TOLERANCES: . <i>X</i> = $\pm .2$ [5] .XX = $\pm .02$ [5] .XXX = $\pm .005$ [.13]	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE A	CAGE CODE 43321	
FRACTIONS $\pm 1/32$ ANGLES $\pm 1^\circ$	COLOR VARIATIONS MAY OCCUR	ITEM NO. LCCA31126	REV. A	
		SCALE: NONE	CAD FILE: LCCA31126.SLDDRW	
			SHEET 1 OF 1	