

Lead Free 1553 TRB 2-Slot Plug to TRB 2-Slot Plug  
Cable Assembly using 30-02001-LC Coax, 5 FT



## LC3MSA00568-60

### Configuration

- Connector 1: TRB 2-Slot Plug
- Connector 2: TRB 2-Slot Plug
- Cable Type: 30-02001-LC

### Features

- MIL-STD-1553
- -20°C to +75°C
- 78 ohms

### Applications

- MIL-STD-1553
- Data

### Description

L-com's LC3MSA00568-60 is a lead free 1553 TRB 2-Slot plug to TRB 2-Slot plug cable assembly using 30-02001-LC coax, 5 FT and ships same-day. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com TRB 2-Slot to TRB 2-Slot cable assembly has a plug to plug gender configuration with 78 Ohm flexible 30-02001-LC series coax and operates to 400 MHz.

Custom versions of this TRB 2-Slot plug to TRB 2-Slot plug cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LC3MSA00568-60 L-com Lead Free 1553 TRB 2-Slot Plug to TRB 2-Slot Plug Cable Assembly using 30-02001-LC Coax, 5 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		400	MHz
Capacitance		19.7 [64.63]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	10	50	100	200	400	MHz
Insertion Loss (Typ.)	0.305	0.45	0.575	0.75	1	dB

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Lead Free 1553 TRB 2-Slot Plug to TRB 2-Slot Plug  
Cable Assembly using 30-02001-LC Coax, 5 FT



## LC3MSA00568-60

### Mechanical Specifications

#### Cable Assembly

Length*	60 in [152.4 cm]
Weight	0.26 lbs [117.93 g]

#### Cable

Cable Type	30-02001-LC
Impedance	78 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Shield Layer 1	Silver Plated Copper
Jacket Material	PVC, Blue
One Time Minimum Bend Radius	2.42 in [61.47 mm]

### Connectors

Description	Connector 1	Connector 2
Type	TRB 2-Slot Plug	TRB 2-Slot Plug
Impedance	78 Ohms	78 Ohms
Contact Material and Plating	Bronze, Gold 30 micro inches	Bronze, Gold 30 micro inches
Contact Plating Specification	ASTM-B-488	ASTM-B-488
Dielectric Type	Teflon	Teflon
Outer Conductor Material and Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Outer Conductor Plating Specification	30 micro inches	30 micro inches
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	ASTM-B-733	ASTM-B-733

### Environmental Specifications

#### Temperature

Operating Range -20 to +75 deg C

### Compliance Certifications

(see [product page](#) for current document)

### Plotted and Other Data

Notes:


Lead Free 1553 TRB 2-Slot Plug to TRB 2-Slot Plug  
Cable Assembly using 30-02001-LC Coax, 5 FT



## LC3MSA00568-60

### How to Order

Part Number Configuration:



Example: LC3MSA00568-12 = 12 inches long cable  
LC3MSA00568-100cm = 100 cm long cable

Lead Free 1553 TRB 2-Slot Plug to TRB 2-Slot Plug Cable Assembly using 30-02001-LC Coax, 5 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Lead Free 1553 TRB 2-Slot Plug to TRB 2-Slot Plug Cable Assembly using 30-02001-LC Coax, 5 FT

L-com CAD Drawing

ZONE	REV	DESCRIPTION	DATE	CHANGED BY
	A	INITIAL RELEASE	8/25/2023	KDANG

## LEAD FREE SOLDER

LENGTH

LABEL

SEE NOTE 1 & 2

WWW.L.COM.COM  
LCXXXXXX-XX

78 OHM TWINAX CABLE  
JACKET: PVC, BLUE  
NOM DIA: 242" [6.15]

2X TRB 2-SLOT PLUG

The diagram illustrates a wiring map for a shielded cable. A vertical line on the left is labeled "SHIELD" at the top and "WHITE" in the middle. To its right, a dashed circle represents a ground plane. Three solid lines extend from the shielded cable to points on the ground plane: a vertical line labeled "WHITE" at its midpoint, a horizontal line labeled "BLUE" at its right end, and a diagonal line labeled "BLACK" at its bottom end. The text "WIRING MAP" is positioned to the right of the ground plane.

## NOTES:

1. CABLE ASSY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROX CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROX 6 INCHES FROM EACH CONNECTOR.  
CABLE ASSEMBLY LENGTH DETERMINED BY ILLUSTRATED:  
LC3MSA00568-XX (-XXX = OAL IN INCHES)  
CABLES ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
- 2.
- 3.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.

 <b>L-com</b> <b>an INFINITE brand</b>		  INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES DIMENSIONS IN ( ) ARE IN MILLIMETERS TOLERANCES:		FRACTIONS $X = 2 [5]$ $\frac{1}{2}$ $\frac{1}{3}$ $XXX = \pm 02 [5]$ $\pm 02$ $\pm 03$	ANGLES $\pm 1^\circ$ SCALE SHEET 1 OF 1
		CABLE LENGTH TOLERANCES: $\pm 12 [305]$ $\pm 12 [305]$ $\pm 12 [305]$ $\pm 60 [1524]$ $\pm 120 [3048]$ $\pm 44 [1021]$ $\pm 120 [3048]$ $\pm 300 [7620]$ $\pm 66 [1521]$ $\pm 300 [7620]$ $\pm 300 [7620]$ $\pm 66 [1521]$	DESCRIPTION Lead Free 2-Slot TRB Plug to Plug 1553 Twinax Cable Using 78 Ohm 30-0201-LC
		Website: <a href="http://www.L-com.com">www.L-com.com</a> Phone: 1.800.341.5266   1.978.682.6936	ITEM NO. <b>L3CMSA00568</b>
		DRAWN BY <b>KDANG</b>	REV <b>A</b>
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE. UNIMPAK IS NOT RESPONSIBLE FOR THE DIMENSIONAL OR MATERIAL SPECIFICATIONS UNLESS THEY ARE LISTED AS CRITICAL FEATURES. UNIMPAK IS NOT RESPONSIBLE FOR THE DIMENSION, SIZE AND LOCATION OF PARTS OR FEATURES WHICH ARE NOT LISTED AS CRITICAL. PARTS OR FEATURES WHICH ARE NOT LISTED AS CRITICAL MAY VARY IN SIZE AND LOCATION AND COLOURS MAY VARY			

LC3MSA00568-60 REV 1.0 | © 2020 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.