

5 Watt RF Load DC to 6 GHz With 2.2-5 Male Brass Body



LCTR1162

Features

- DC to 6 GHz Frequency Range
- 50 Ohm Impedance
- 2.2-5 Male Coaxial Interface
- Max VSWR 1.25:1
- Max Power 5 Watts (CW)

Applications

- 5G Cellular bands
- Radar Systems
- Commercial and Military Communication
- SatCom
- Test and Measurement

Description

L-com's PE6TR1162 is an RF termination (also called RF load or dummy load) that operates from DC to 6 GHz and handles up to 5 Watt (CW). Our 2.2-5 termination / load has a male gender. PE6TR1162 2.2-5 load termination offers 1.25:1 max VSWR.

RF load / terminations are indispensable components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can potentially damage the device or reduce the signal integrity. By using a terminator on an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, circulators, and switches. They are also widely used in measurement systems to ensure accurate results. L-com offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watt (CW).

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
Impedance		50		Ohms
VSWR			1.25:1	
Input Power (CW)			5	Watts
Input Power (Peak)			50	Watts
8% Duty Cycle, 20us PW				

Mechanical Specifications

Size

Length	1.38 in [35.05 mm]
Width	0.63 in [16 mm]
Height	0.63 in [16 mm]
Weight	0.11 lbs [49.9 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[5 Watt RF Load DC to 6 GHz With 2.2-5 Male Brass Body LCTR1162](#)

5 Watt RF Load DC to 6 GHz With 2.2-5 Male Brass Body



LCTR1162

Configuration

Connector

2.2-5 Male

Material Specifications

Description	Material	Plating
Connector 1 Contact	Beryllium Copper	Silver
Insulation	PTFE	
Body	Brass	Copper-Tin-Zinc Alloy
Housing	Brass	Tri-Metal

Environmental Specifications

Temperature

Operating Range

-40 to +75 deg C

Storage Range

-50 to +85 deg C

Humidity

<95%

Shock

IEC 60068-2-27

Vibration

IEC 60068-2-6-Fc

Altitude

<5000m

Thermal Shock

IEC 60068 -2-14-Na

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

5 Watt RF Load DC to 6 GHz With 2.2-5 Male Brass Body from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 5 Watt RF Load DC to 6 GHz With 2.2-5 Male Brass Body LCTR1162

URL: <https://www.l-com.com/6ghz-5w-rf-termination-2.2-5-male-lctr1162-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

