

Low Loss Flexible LMR-200-FR Fire Rated Coax Cable Double Shielded with Black FRPE Jacket By The Foot

LMR-200-FR-LC





Phase Velocity 83% VoP

Max operating Frequency of 5.8 GHz

Configuration

- Low Loss, Fire Flexible Cable
- 2 Shield(s)

Features

- FRPE Jacket
- Max operating temperature 185°C
- Min Install Bend radius of 2 inches

Applications

- Antenna Installs
- RF Test systems

- · General Purpose RF Interconnect
- Laboratory applications

Description

LMR-200-FR-LC coax cable from L-com is only one of a large number of radio frequency coaxial cable types specifically stocked to be ready for quick shipment. L-com Microwave LMR-200-FR-LC coax cable is manufactured in a flexible design and has a 50 Ohm impedance. This low loss flexible 50 Ohm coax cable LMR-200-FR-LC is constructed with a 0.195 inch diameter and Black FRPE jacket.

LMR-200-FR-LC flexible 50 Ohm coax cable with FRPE jacket is rated for a 5.8 GHz maximum operating frequency. This 50 Ohm 0.195 inch diameter and low loss flexible coax cable is built with a double shield count and RF shielding of 90 dB. L-com Microwave LMR-200-FR-LC coax is constructed with PE dielectric and a maximum operating temperature of 185 degrees C. Times Microwave LMR-200-FR-LC coax cable specs for this wire properties can be found on its RF coax cable LMR-200-FR-LC datasheet.

LMR-200-FR-LC cable is part of more than one million RF, microwave parts in stock at L-com. This Times Microwave low loss LMR-200-FR-LC coax cable is ready to buy and can be shipped worldwide. L-com also maintains a wide selection of other radio frequency coaxial cable types that ship same-day from our warehouse as with the rest of our other RF/microwave components.

* LMR™ is a trademark of Times Microwave Systems.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
Impedance		50		Ohms
Velocity of Propagation		83		%
Shielding Effectiveness	90			dB
Dielectric Withstanding Voltag	ge (DC)		1,000	Vdc
Jacket Spark			3,000	Vrms
Nominal Capacitance		24.5 [80.38]		pF/ft [pF/m]
Nominal Inductance		0.061 [0.2]		uH/ft [uH/m]
Input Power (Peak)			2.5	kWatts



Low Loss Flexible LMR-200-FR Fire Rated Coax Cable Double Shielded with Black FRPE Jacket By The Foot



LMR-200-FR-LC



Performance by Frequency Band

Description	F1	F2	F3	F4	F5	Units
Frequency	50	150	220	450	900	MHz
Attenuation, Typ	2.3	4	4.8	7	9.9	dB/100ft
	7.55	13.12	15.75	22.97	32.48	dB/100m
Input Power (CW), Max	790	450	370	260	180	Watts
Description	F6	F7	F8	F9	F10	Units
Frequency	1.8	2.5	5.8			GHz
Attenuation, Typ	14.2	16.9	26.4			dB/100ft
	46.59	55.45	86.61			dB/100m
Input Power (CW), Max	130	110	70			Watts

Mechanical Specifications

Diameter
Weight
Min. Bend Radius (Installation)
Min. Bend Radius (Repeated)
Bending Moment
Tensile Strength
Flat Plate Crush

0.195 in [4.95 mm] 0.026 lbs/ft [0.04 Kg/m] 0.5 in [12.7 mm] 2 in [50.8 mm] 2 lbs-ft [2.71 N-m] 40 lbs [18.14 kg] 15 lbs/in [0.27 Kg/mm]

Construction Specifications

Description	Material and Plating	Diameter
Inner Conductor	Copper 1 Strand(s)	0.044in [1.12mm]
Conductor Type	Solid	
Dielectric	PE	0.116in [2.95mm]
First Shield	Aluminum Tape	
Second Shield	Tinned Copper Braid	
Jacket	FRPE, Black	0.195in [4.95mm]



Low Loss Flexible LMR-200-FR Fire Rated Coax Cable Double Shielded with Black FRPE Jacket By The Foot

LMR-200-FR-LC



TIMES MICROWAVE SYSTEMS

Environmental Specifications

Temperature Operating Range Storage Range


-40°C to +185°C -94°C to +185°C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Low Loss Flexible LMR-200-FR Fire Rated Coax Cable Double Shielded with Black FRPE Jacket By The Foot from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.



Low Loss Flexible LMR-200-FR Fire Rated Coax Cable Double Shielded with Black FRPE Jacket By The Foot

L-com CAD Drawing