

Hand Formable Test Probe SMA Female to Straight Cut Lead Cable Assembly using LC047TB Coax, Gold Plated Brass Body, 9 IN



LCCA30708-9IN

Configuration


- Connector 1: SMA Female
- Connector 2: Straight Cut Lead
- Cable Type: LC047TB

Features

- 100% RF Tested prior to final trim
- 1.4 Max VSWR to 18 GHz
- 100% High Pot Tested to 500V
- 0.047 Diameter Formable coax
- Individually packed in protective tube

Applications

- Used as an RF Test Probe to 18 GHz
- RF PCB Board Measurements
- Signal Injection



Description

L-com's LCCA30708-9IN is a Test Probe SMA Female to Straight Cut Lead Cable Assembly using LC047TB Coax, 0.75 FT and ships same-day. L-com's formable cable assemblies provide a convenient alternative to their semi-rigid versions, as they offer similar electrical performance but can be bent to desired shape without the use of special tools. Our L-com SMA to flush cut cable assembly has a Female to sexless gender configuration with formable LC047TB series coax and operates to 18 GHz. The tinned copper braid outer conductor can be easily formed by hand and has an overall diameter of 0.047 inches.

The Test Probe SMA Female to Straight Cut Lead Cable Assembly using LC047TB Coax, 0.75 FT is a convenient test probe designed to be trimmed by the user to their required dimensions and soldered to an exposed microstrip trace to inject a signal or to measure a signal of interest. Each LCCA30708-9IN cable assembly is built with a connector on both ends to verify the electrical performance of 18 GHz with a maximum VSWR of 1.4:1. The cable is then trimmed and placed in a reusable protective tube. These test probes are available with a flush cut or a pre-trimmed cable lead.

Custom versions of this SMA Female to straight cut lead cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30708-9IN L-com Test Probe SMA Female to Straight Cut Lead Cable Assembly using LC047TB Coax data sheet PDF include details of the RF product specifications, CAD drawing(s) and dimensions below.

Hand Formable Test Probe SMA Female to Straight Cut Lead Cable Assembly using LC047TB Coax, Gold Plated Brass Body, 9 IN

LCCA30708-9IN



Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-----------------|---------|-------------|---------|--------------|
| Frequency Range | DC | | 18 | GHz |
| VSWR | | | 1.4:1 | |
| Capacitance | | 32 [104.99] | | pF/ft [pF/m] |

Mechanical Specifications

Cable Assembly

| | |
|--------|-------------------|
| Length | 9 in [228.6 mm] |
| Weight | 0.01 lbs [4.54 g] |

Cable

| | |
|--------------------------------------|---------------------------|
| Cable Type | LC047TB |
| Impedance | 50 Ohms |
| Inner Conductor Type | Solid |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type | PTFE |
| Number of Shields | 1 |
| Shield Layer 1 | Tinned Copper Braid |
| Jacket Diameter | 0.047 in [1.19 mm] |

Connectors

| Description | Connector 1 | Connector 2 |
|-------------------------------|------------------------|-------------------|
| Type | SMA Female | Straight Cut Lead |
| Specification | MIL-STD-348A | |
| Impedance | 50 Ohms | |
| Contact Material and Plating | Beryllium Copper, Gold | |
| Contact Plating Specification | 50µ in. minimum | |
| Dielectric Type | Teflon | |
| Body Material and Plating | Brass, Gold | |
| Body Plating Specification | 30µ in. minimum | |

Hand Formable Test Probe SMA Female to Straight Cut Lead Cable Assembly using LC047TB Coax, Gold Plated Brass Body, 9 IN

LCCA30708-9IN



Compliance Certifications (see [product page](#) for current document)


Plotted and Other Data

Notes:

- Values at 25°C, sea level.

How to Order

Part Number Configuration:



Example: LCCA30708-12 = 12 inches long cable
LCCA30708-100cm = 100 cm long cable

Hand Formable Test Probe SMA Female to Straight Cut Lead Cable Assembly using LC047TB Coax, Gold Plated Brass Body, 9 IN from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Hand Formable Test Probe SMA Female to Straight Cut Lead Cable
Assembly using LC047TB Coax, Gold Plated Brass Body, 9 IN

L-com CAD Drawing

