

Low Loss N Male Right Angle to N Male Weatherproof Cable Assembly with Silicone using SPO-250 Coax, 0.5M with Times Microwave Components



LCCA9879/WP-M0.5

Configuration

- Connector 1: N Male Right Angle
- Connector 2: N Male
- Cable Type: SPO-250
- Coax Flex Type: Flexible

Features

- Silicone Connector Boot
- IP68 Rated

Description

L-com's LCCA9879/WP-M0.5 is a low loss N male right angle to N male weatherproof cable assembly with silicone using SPO-250 coax, 0.5M with Times Microwave components and ships same-day. The SPO-250 coax of this N cable uses the foam PE dielectric with a VoP of 83%, resulting in very low insertion loss compared to solid dielectrics. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com N to N cable assembly has a male to male gender configuration with flexible SPO-250 series coax and operates to 6 GHz. This right angle N cable interface on the SPO-250 coax allows for easier connections in tight spaces.

Custom versions of this N male to N male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA9879/WP-M0.5 L-com Low Loss N Male Right Angle to N Male Weatherproof Cable Assembly with Silicone using SPO-250 Coax, 0.5M with Times Microwave Components data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		83		%
Passive Intermodulation			-160	dBc
IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz				
Capacitance		24 [78.74]		pF/ft [pF/m]
Inductance		0.054 [0.18]		uH/ft [uH/m]

Specifications by Frequency

Low Loss N Male Right Angle to N Male Weatherproof
Cable Assembly with Silicone using SPO-250 Coax,
0.5M with Times Microwave Components



LCCA9879/WP-M0.5

Part Number	Length	Description	F1	F2	F3	F4	Units	Weight (lbs)
		Frequency	500	1000	2500	6000	MHz	
LCCA9879/WP	Custom Lengths Available	Insertion Loss (Typ.)	0.057	0.041	0.068	0.108	dB/ft	
			0.19	0.14	0.23	0.36	dB/m	
LCCA9879/WP-FT2	24 in	Insertion Loss (Typ.)	0.33	0.39	0.5	0.67	dB	0.741
LCCA9879/WP-FT3	36 in	Insertion Loss (Typ.)	0.36	0.43	0.57	0.77	dB	0.788
LCCA9879/WP-FT5	60 in	Insertion Loss (Typ.)	0.42	0.51	0.7	0.99	dB	0.882
LCCA9879/WP-M0.5	50 CM	Insertion Loss (Typ.)	0.32	0.37	0.47	0.63	dB	0.725

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.2 dB

Loss due to Connector 2: 0.1*SQRT(FGHz) dB

Base Weight: 0.694 pounds

Additional Weight per Inch: 0.00391 pounds

Mechanical Specifications

Cable Assembly

Length	19.685 in [500 mm]
Width/Diameter	0.5 in [12.7 mm]
Weight	0.725 lbs [328.85 g]

Cable

Cable Type	SPO-250
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Aluminum
Dielectric Type	Foam PE
Outer Conductor 1 Material and Plating	Copper, Corrugated
Jacket Material	PE
Jacket Diameter	0.303 in [7.7 mm]
One Time Minimum Bend Radius	1 in [25.4 mm]
Bending Moment	0.5 lbs-ft [0.68 N-m]

Low Loss N Male Right Angle to N Male Weatherproof Cable Assembly with Silicone using SPO-250 Coax, 0.5M with Times Microwave Components



LCCA9879/WP-M0.5

Connectors

Description	Connector 1	Connector 2
Type	N Male Right Angle	N Male
Option		Weatherproof Boot
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Straight
Contact Material and Plating	Brass, Silver	Phosphor Bronze, Silver
Contact Plating Specification	200 μ in minimum	196 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	100 μ in minimum	118 μ in minimum
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Plating Specification	100 μ in minimum	118 μ in minimum
Boot Material	Silicone	Silicone

Environmental Specifications

Operating Range Temperature: -40 to +85 deg C
 Ingress Protection (IP) Rating: IP68

Compliance Certifications

(see [product page](#) for current document)

Plotted and Other Data

Notes:
 Values at 25°C, sea level.

Low Loss N Male Right Angle to N Male Weatherproof Cable Assembly with Silicone using SPO-250 Coax, 0.5M with Times Microwave Components




LCCA9879/WP-M0.5

Typical Performance Data

How to Order

Part Number Configuration:



Example: LCCA9879/WP-12 = 12 inches long cable
LCCA9879/WP-100cm = 100 cm long cable


Low Loss N Male Right Angle to N Male Weatherproof Cable Assembly with Silicone using SPO-250 Coax, 0.5M with Times Microwave Components from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/n-male-n-male-cable-assembly-lcca9879-wp-m0.5-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

LCCA9879/WP-M0.5 CAD Drawing

Low Loss N Male Right Angle to N Male Weatherproof Cable Assembly with Silicone using SPO-250 Coax, 0.5M with Times Microwave Components



NOTES.

NOTES.

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 84 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 84 INCHES, TWO LABELS APPROXIMATELY 12 INCHES FROM EACH CONNECTOR.
2. PIM LABEL PLACEMENT FOR ALL LENGTHS: 6 INCHES FROM CABLE END, 1 PLACE.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
4. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO US LAW PROHIBITED.