	8	/	6		5 🔸		1	3	2		
PROPERTY OF	ATION CONTAINED IN THIS E L-COM, INC. ANY REPRODU WRITTEN PERMISSION OF L-CO	DRAWING IS THE SOLE					REV		REVISIONS DESCRIPTION	DATE	APPROVED
/ITHOUT THE \	WRITTEN PERMISSION OF L-CC	DM, INC. IS PROHIBITED.						ITIAL RELEASE		4/21/10	D.GRIFFIN
	DESCRIPTION	MATERIAL	FINISH								
	BODY	BRASS	NICKEL								
	CENTER PIN	BRASS	GOLD								
	INSULATOR	ACETAL	-								
					(1.45)		1				
				-	$ \left(\begin{array}{c} 1.45\\ [37] \end{array}\right)$		-				
						炎					
						ᅠ					
						⊗					
						8					
						🕺					
						8					
							Ľ				
				$\vee \vee \vee \square$		⊴───	, ,				
						\backslash					
						,	\				
							─2X 5,	'8-24 UNEF			
N	IOTES.										
N	IOTES:										
E											
EI IA	LECTRICAL: MPEDANCE: 50 OHM	1S			Ro	HS Comp	liant	· •			
EI IA FI	ELECTRICAL: MPEDANCE: 50 OHM REQUENCY RANGE:	DC ~ 11 GHz			Ro	HS Comp	liant				
EI IA FI V	ELECTRICAL: MPEDANCE: 50 OHM REQUENCY RANGE: 11/0LTAGE RATING: 15	DC ~ 11 GHz 500 VOLTS PEAK				HS Comp					
EI IN FI V	ELECTRICAL: MPEDANCE: 50 OHM REQUENCY RANGE:	DC ~ 11 GHz 500 VOLTS PEAK E: 2500V RMS.			UNLES	S OTHERWISE SPECIFIED, IONS ARE IN INCHES [mm]	APPROVAL DRAWN BY	S DATE		Giobal Coppositivity NORTH A	NDOVER, MA
EI IA FI V	ELECTRICAL: MPEDANCE: 50 OHM REQUENCY RANGE: OLTAGE RATING: 15 VITHSTAND VOLTAGI NSERTION LOSS: .15 (DC ~ 11 GHz 500 VOLTS PEAK E: 2500V RMS.			UNLES	S OTHERWISE SPECIFIED, IONS ARE IN INCHES [mm]	APPROVAL DRAWN BY D. CASTRO CHECKED BY	S DATE 4/20/10		Giobal Coppositivity NORTH A	
EI IA FI V IN	ELECTRICAL: MPEDANCE: 50 OHM REQUENCY RANGE: OLTAGE RATING: 15 VITHSTAND VOLTAGI NSERTION LOSS: .15 (AISCELLANEOUS:	DC ~ 11 GHz 500 VOLTS PEAK E: 2500V RMS. dB MAX.			UNLES	S OTHERWISE SPECIFIED, IONS ARE IN INCHES [mm]	APPROVAL DRAWN BY D. CASTRO CHECKED BY K. BURGNER APPROVED BY	S DATE 4/20/10 4/21/10		Connectivity NORTH A	NDOVER, MA
EI IA FI V M IN	ELECTRICAL: MPEDANCE: 50 OHM REQUENCY RANGE: (OLTAGE RATING: 12 VITHSTAND VOLTAGI NSERTION LOSS: .15 (AISCELLANEOUS: COMPONENT SHALL	DC ~ 11 GHz 500 VOLTS PEAK E: 2500V RMS. dB MAX. BE INDIVIDUALLY P	ACKAGED IN		UNLES DIMENS OVERALL > 12 [30 > 60 [1524 > 120 [304 > 30	S OTHERWISE SPECIFIED, IONS ARE IN INCHES [mm] CABLE LENGTH TOLERANCE: 2 [305] = +1 [25] / -0 5 [300] [324] = +2 [51] / -0] = 120 [3048] = +4 [102] / -0 3 [300] [7620] = +6 [152] / -0 00 [7620] = +5% / -0%	APPROVAL DRAWN BY D. CASTRO CHECKED BY K. BURGNER	S DATE 4/20/10	CATEGORY	Giobal Coppositivity NORTH A	NDOVER, MA
EI IA FI V M IN	ELECTRICAL: MPEDANCE: 50 OHM REQUENCY RANGE: OLTAGE RATING: 15 VITHSTAND VOLTAGI NSERTION LOSS: .15 (AISCELLANEOUS:	DC ~ 11 GHz 500 VOLTS PEAK E: 2500V RMS. dB MAX. BE INDIVIDUALLY P	ACKAGED IN 2031		UNLES DIMENS OVERALL > 12 [30 > 60 [1524 > 120 [304 > 30	S OTHERWISE SPECIFIED, IONS ARE IN INCHES [mm] CABLE LENGTH TOLERANCE: 2 [305] = +1 [25] / -0 5 [300] [324] = +2 [51] / -0] = 120 [3048] = +4 [102] / -0 3 [300] [7620] = +6 [152] / -0 00 [7620] = +5% / -0%	APPROVAL DRAWN BY D. CASTRO CHECKED BY K. BURGNER APPROVED BY K. BURGNER	S DATE 4/20/10 4/21/10 4/21/10		Connectivity NORTH A	NDOVER, MA 01845
EI I∧ Fi V M IՒ C A	ELECTRICAL: MPEDANCE: 50 OHM REQUENCY RANGE: (OLTAGE RATING: 12 VITHSTAND VOLTAGI NSERTION LOSS: .15 (AISCELLANEOUS: COMPONENT SHALL	DC ~ 11 GHz 500 VOLTS PEAK E: 2500V RMS. dB MAX. BE INDIVIDUALLY P I L-COM SPEC. PS-0	0031		UNLES DIMENS OVERALL > 12 [30 > 60 [1524 > 120 [304 > 30	S OTHERWISE SPECIFIED, IONS ARE IN INCHES [mm]	APPROVAL DRAWN BY D. CASTRO CHECKED BY K. BURGNER APPROVED BY K. BURGNER CONFIGU UNDIMEN	S DATE 4/20/10 4/21/10		Connectivity NORTH A	
EI IN FI V M IN C A	ELECTRICAL: MPEDANCE: 50 OHA REQUENCY RANGE: VOLTAGE RATING: 15 VITHSTAND VOLTAGI NSERTION LOSS: .15 O AISCELLANEOUS: COMPONENT SHALL ACCORDANCE WITH	DC ~ 11 GHz 500 VOLTS PEAK E: 2500V RMS. dB MAX. BE INDIVIDUALLY P I L-COM SPEC. PS-0	0031		UNLES DIMENS OVERALL > 12 [30 > 60 [1524 > 120 [304 > 30	S OTHERWISE SPECIFIED, IONS ARE IN INCHES [mm] CABLE LENGTH TOLERANCE: 2 [305] =+1 [25] /-0 5] 560 [1524] =+2 [51] /-0 5] 560 [1524] =+4 [102] /-0 0 [7620] =+5(152] /-0 0 [7620] =+5(152] /-0 DIMENSIONAL TOLERANCES: X = ± .0 .XXX = ±.005	APPROVAL DRAWN BY D. CASTRO CHECKED BY K. BURGNER APPROVED BY K. BURGNER CONFIGU UNDIMEN N	S DATE 4/20/10 4/21/10 4/21/10 RATION DETAILS OF ISIONED FEATURES IAY VARY	CATEGORY CC PRODUCT DESCRIPTION ADP, N-FEM SIZE FSCM NO. DWG.	OAXIAL ALE TO N-FEMA	NDOVER, MA 11845
EI IA FI V M IN C A	ELECTRICAL: MPEDANCE: 50 OHA REQUENCY RANGE: VOLTAGE RATING: 15 VITHSTAND VOLTAGI NSERTION LOSS: .15 O AISCELLANEOUS: COMPONENT SHALL ACCORDANCE WITH	DC ~ 11 GHz 500 VOLTS PEAK E: 2500V RMS. dB MAX. BE INDIVIDUALLY P I L-COM SPEC. PS-0	0031		UNLES DIMENS OVERALL >12 [30 >60 [152 >120 [304 >30 ALL OTHER	S OTHERWISE SPECIFIED, IONS ARE IN INCHES [mm] CABLE LENGTH TOLERANCE: 2 [305] =+1 [25] /-0 5] 560 [1524] =+2 [51] /-0 5] 560 [1524] =+4 [102] /-0 0 [7620] =+5(152] /-0 0 [7620] =+5(152] /-0 DIMENSIONAL TOLERANCES: X = ± .0 .XXX = ±.005	APPROVAL DRAWN BY D. CASTRO CHECKED BY K. BURGNER APPROVED BY K. BURGNER CONFIGU UNDIMEN N	S DATE 4/20/10 4/21/10 4/21/10 RATION DETAILS OF RATION DETAILS OF	CATEGORY CCC PRODUCT DESCRIPTION ADP, N-FEM	Connectivity NORTH A CONNECTIVITY OF CONTRACT CONTRACTOR CONTRACTOR CONTRACTOR CONTRACTOR CONTRACTOR CONTRACTOR CONTRACTOR CONTRACTOR CONNECTIVITY CONNECTIVI CONNECTIVITY CONNECTIVI CONNECTIVITY CONNECTIVITY CONNE	NDOVER, MA 11845