


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/16/12	D.GRIFFIN



WIRE CHART		
"P1"	COLOR	"J1"
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	VIOLET	8
9	GRAY	9
10	WHITE	10
11	PINK	11
12	LIGHT GREEN	12
13	BLACK/WHITE	13
14	BROWN/WHITE	14
15	RED/WHITE	15
SHELL	DRAIN WIRE	SHELL

MODEL NUMBER	LENGTH	
	FEET	METERS
CS2NB15MF-1	1.0	0.31
CS2NB15MF-2.5	2.5	0.76
CS2NB15MF-5	5.0	1.52
CS2NB15MF-10	10.0	3.05
CS2NB15MF-15	15.0	4.57
CS2NB15MF-25	25.0	7.62
CS2NB15MF-50	50.0	15.24

**NOTES:**

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY D.DESJARDIN CHECKED BY D.FRISIELLO APPROVED BY S.SMITH	DATE 2/13/12 2/13/12 2/13/12	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		CATEGORY D-SUBMINIATURE PRODUCT DESCRIPTION DB15 M/F PREMIUM MOLDED CABLE
SCALE: NONE		FSCM NO. <b>A</b> 43321	DWG. NO. CS2NB15MF	REV. <b>A</b>
CAD FILE: CS2NB15MF.SLDDRW		SHEET 1 OF 1		