


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES DG259FM-IBM-OD1	7/11/14	D.FRISIELLO

WIRE CHART	
DB9M	DB25F
PIN 1	PIN 8
PIN 2	PIN 3
PIN 3	PIN 2
PIN 4	PIN 20
PIN 5	PIN 7
PIN 6	PIN 6
PIN 7	PIN 4
PIN 8	PIN 5
PIN 9	PIN 22
SHELL	SHELL



NOTES:

- INTERNAL 360° COPPER FOIL SHIELD HAS DRAIN WIRE SOLDERED TO METAL FRAME OF BOTH CONNECTORS.
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	APPROVALS DRAWN BY TJC CHECKED BY DFP APPROVED BY CM	DATE 11/8/01 1/11/02 1/11/02	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY D-SUBMINIATURE		
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. DG259FM-IBM	REV. A
	SCALE: NONE		CAD FILE: DG259FM-IBM.SLDDRW		SHEET 1 OF 1	