




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/3/15	D.GRIFFIN
B	ECN 8113: UPDATE STRANDED CONDUCTOR TO SOLID FOR CABLE	10/14/15	S.LI



UL 20276
 (5) INDIVIDUAL TWISTED PAIR 32AWG SOLID TINNED COPPER WITH ALUM/POLY FOIL SHIELD AND DRAIN WIRE.
 (4) CONDUCTOR 32AWG SOLID TINNED COPPER WITH ALUM/POLY FOIL SHIELD AND TINNED COPPER DRAIN WIRE PLUS TINNED COPPER BRAID SHIELD.
 JACKET: PVC, BLACK (NOM. DIA: .216" [5.50])



NOTES:

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU (RoHS DIRECTIVE)

MODEL NUMBER	LENGTH METERS [FEET]
DPCAC2MM-0.5M	0.5 [1.64]
DPCAC2MM-1M	1.0 [3.28]
DPCAC2MM-2M	2.0 [6.56]
DPCAC2MM-3M	3.0 [9.84]
DPCAC2MM-5M	5.0 [16.41]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.3]	APPROVALS DRAWN BY D.FRISIELLO	DATE 4/4/14	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CHECKED BY R.SCOTT	DATE 4/4/14	
APPROVED BY S.SMITH	DATE 4/4/14	PRODUCT DESCRIPTION CA DP M/MINI DP M	
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
		DWG. NO. DPCAC2MM	REV. B
		SCALE: NONE	CAD FILE: DPCAC2MM.SLDDRW
		SHEET 1 OF 1	