


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	05/24/2023	HBAKKE	AGANWANI



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	L-COM™ an INFINITI® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
OVERALL CABLE LENGTH TOLERANCE:	DRAWN BY	5/10/2023	CATEGORY		COAXIAL
$\leq 12 [305] = +1 [25] / -0$ $> 12 [305] \leq 60 [1524] = +2 [51] / -0$ $> 60 [1524] \leq 120 [3048] = +4 [102] / -0$ $> 120 [3048] \leq 300 [7620] = +6 [152] / -0$ $> 300 [7620] = +5\% / -0$	CHECKED BY	05/24/2023	PRODUCT DESCRIPTION		Reverse Polarity SMA Jack to Reverse Polarity SMA Plug Right Angle Cable Using RG174 Coax , LF Solder
ALL OTHER DIMENSIONAL TOLERANCES:	APPROVED BY	05/24/2023	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE	CAGE CODE
$.X = \pm .2 [5]$ $.XX = \pm .02 [5]$ $.XXX = \pm .005 [1.3]$	KLEITLEN			A	43321
			THIRD-ANGLE PROJECTION	COLOR VARIATIONS MAY OCCUR	ITEM NO.
					LCCA31118
				SCALE: NONE	CAD FILE: LCCA31118.SLDDRW
					SHEET 1 OF 1