

Lead Free 1553 TRB 2-Slot Plug to Blunt Cut Genderless Cable Assembly using 30-02001-LC Coax, 2 FT



LC3MSA00569-24

Configuration

- Connector 1: TRB 2-Slot Plug
- Connector 2: Blunt Cut Genderless
- Cable Type: 30-02001-LC

Features

- MIL-STD-1553
- -20°C to +75°C
- 78 ohms

Applications

- MIL-STD-1553
- Data

Description

L-com's LC3MSA00569-24 is a lead free 1553 TRB 2-Slot plug to blunt cut genderless cable assembly using 30-02001-LC coax, 2 FT and ships same-day. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com TRB 2-Slot to Blunt Cut cable assembly has a plug to genderless gender configuration with 78 Ohm flexible 30-02001-LC series coax and operates to 400 MHz.

Custom versions of this TRB 2-Slot plug to TRB 2-Slot genderless cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LC3MSA00569-24 L-com Lead Free 1553 TRB 2-Slot Plug to Blunt Cut Genderless Cable Assembly using 30-02001-LC Coax, 2 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		400	MHz
Capacitance		19.7 [64.63]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	10	50	100	200	400	MHz
Insertion Loss (Typ.)	0.242	0.3	0.35	0.42	0.52	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Lead Free 1553 TRB 2-Slot Plug to Blunt Cut Genderless
Cable Assembly using 30-02001-LC Coax, 2 FT



LC3MSA00569-24

Mechanical Specifications

Cable Assembly

Length*	24 in [609.6 mm]
Weight	0.1518 lbs [68.86 g]

Cable

Cable Type	30-02001-LC
Impedance	78 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Shield Layer 1	Silver Plated Copper
Jacket Material	PVC, Blue

One Time Minimum Bend Radius	2.42 in [61.47 mm]
------------------------------	--------------------

Connectors

Description	Connector 1	Connector 2
Type	TRB 2-Slot Plug	Blunt Cut Genderless
Impedance	78 Ohms	
Contact Material and Plating	Bronze, Gold 30 micro inches	
Contact Plating Specification	ASTM-B-488	
Dielectric Type	Teflon	
Outer Conductor Material and Plating	Phosphor Bronze, Gold	
Outer Conductor Plating Specification	30 micro inches	
Body Material and Plating	Brass, Nickel	
Body Plating Specification	ASTM-B-733	

Environmental Specifications

Temperature

Operating Range	-20 to +75 deg C
-----------------	------------------

Compliance Certifications

(see [product page](#) for current document)

Plotted and Other Data

Notes:


Lead Free 1553 TRB 2-Slot Plug to Blunt Cut Genderless
Cable Assembly using 30-02001-LC Coax, 2 FT



LC3MSA00569-24

How to Order

Part Number Configuration:



Example: LC3MSA00569-12 = 12 inches long cable
LC3MSA00569-100cm = 100 cm long cable

Lead Free 1553 TRB 2-Slot Plug to Blunt Cut Genderless Cable Assembly using 30-02001-LC Coax, 2 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

LEAD FREE SOLDER

ZONE	RE	μ
------	----	-------

com CAD Drawing

The diagram illustrates the assembly of a TRB 2-Slot Plug. It features a central vertical tube with a flared bottom. A horizontal cable is inserted into the tube, with its end terminating in a TRB 2-SLOT PLUG. The cable is labeled "78 OHM TWINAX CABLE JACKET: PVC, BLUE NOM. DIA: .242" [6.15]. A label on the tube indicates "WWW1-COM COM LCXXXXXX-XX" and includes "SEE NOTE 1 & 2". The total length of the assembly is marked as "LENGTH". A "BLUNT CUT" is indicated at the top of the tube.

NOTES:

1. CABLE ASSY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROX CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROX 6 INCHES FROM EACH CONNECTOR.
CABLE ASSEMBLY LENGTH DETERMINED BY ILLUSTRATED:
LC3MMSA00569-XX (-XX = OAL IN INCHES)
CABLES ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
- 2.
- 3.

 L-com® an INFINITE brand Website: www.L-com.com Phone: 1.800.341.5266 1.978.682.6936		INTERPRET ALL DIMENSIONS IN INCHES UNLESS OTHERWISE SPECIFIED. LEADING DIMENSIONS ARE IN INCHES. DIMENSIONS IN [] ARE IN MILLIMETERS. TOLERANCES: $X = \pm 0.2 [5]$ FRACTIONS $XX = \pm 0.05 [0.5]$ $\pm 1/32$ $XXX = \pm 0.005 [0.13]$ ANGLES S. T. CABLE LENGTH TOLERANCES: $\pm 12 [305]$ $\pm 1 [25]$ $\pm 60 [1524]$ $\pm 2 [50]$ $\pm 304 [7620]$ $\pm 4 [102]$ $\pm 152 [3848]$ $\pm 6 [152]$ $\pm 76 [1930]$ $\pm 10 [254]$ $\pm 38 [965]$ $\pm 15 [381]$		INTERPRET ALL DIMENSIONS AS Y14.5 TOLERANCES PER ASME Y14.5. SCALE: 1 OF 1 SHEET 1 1	
		DESCRIPTION Lead Free 2-Slot TRB Plug with Blunt Cut 1553 Twinax Cable Using 78 Ohm 30-0200-1-LC			
ITEM NO. LC3MSA00569	ITEM NO. LC3MSA00569	SIZE A	CAGE CODE 43321	DRAWN BY KDANG	
1	2				
3					