

Lead Free 1553 TRB 3-Slot Plug to TRB 2-Slot Plug Cable Assembly using 30-02001-LC Coax, 1 FT with Bend Relief

## LC3MSA00571-12



### Configuration

- Connector 1: TRB 3-Slot Plug
- Connector 2: TRB 2-Slot Plug
- Cable Type: 30-02001-LC

### Features

- MIL-STD-1553
- -20°C to +75°C
- 78 ohms

### Applications

- MIL-STD-1553
- Data

### Description

L-com's LC3MSA00571-12 is a lead free 1553 TRB 3-Slot plug to TRB 2-Slot plug cable assembly using 30-02001-LC coax, 1 FT with bend relief and ships same-day. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com TRB 3-Slot to TRB 2-Slot cable assembly has a plug to plug gender configuration with 78 Ohm flexible 30-02001-LC series coax and operates to 400 MHz.

Custom versions of this TRB 3-Slot plug to TRB 3-Slot plug cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LC3MSA00571-12 L-com Lead Free 1553 TRB 3-Slot Plug to TRB 2-Slot Plug Cable Assembly using 30-02001-LC Coax, 1 FT with Bend Relief data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		400	MHz
Capacitance		19.7 [64.63]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

#### Insertion Loss (Typ.)

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

### Mechanical Specifications

#### Cable Assembly

- Length\* 12 in [304.8 mm]
- Weight 0.1078 lbs [48.9 g]

#### Cable

- Cable Type 30-02001-LC
- Impedance 78 Ohms

Lead Free 1553 TRB 3-Slot Plug to TRB 2-Slot Plug Cable Assembly using 30-02001-LC Coax, 1 FT with Bend Relief



## LC3MSA00571-12

Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Shield Layer 1	Silver Plated Copper
Jacket Material	PVC, Blue
One Time Minimum Bend Radius	2.42 in [61.47 mm]

### Connectors

Description	Connector 1	Connector 2
Type	TRB 3-Slot Plug	TRB 2-Slot Plug
Impedance	78 Ohms	78 Ohms
Contact Material and Plating	Bronze, Gold 30 micro inches	Bronze, Gold 30 micro inches
Contact Plating Specification	ASTM-B-488	ASTM-B-488
Dielectric Type	Teflon	Teflon
Outer Conductor Material and Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Outer Conductor Plating Specification	30 micro inches	30 micro inches
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	ASTM-B-733	ASTM-B-733

### Environmental Specifications

#### Temperature

Operating Range

-20 to +75 deg C

### Compliance Certifications

(see [product page](#) for current document)

### Plotted and Other Data

Notes:


Lead Free 1553 TRB 3-Slot Plug to TRB 2-Slot Plug Cable Assembly using 30-02001-LC Coax, 1 FT with Bend Relief

## LC3MSA00571-12



### How to Order

Part Number Configuration:



Example: LC3MSA00571-12 = 12 inches long cable  
LC3MSA00571-100cm = 100 cm long cable

Lead Free 1553 TRB 3-Slot Plug to TRB 2-Slot Plug Cable Assembly using 30-02001-LC Coax, 1 FT with Bend Relief from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Lead Free 1553 TRB 3-Slot Plug to TRB 2-Slot Plug Cable Assembly  
using 30-02001-LC Coax, 1 FT with Bend Relief

L-com CAD Drawing

ZONE	REV	A
------	-----	---

## LEAD FREE SOLDER

ENCLOSURE

—LABEL  
SEE NOTE 1 & 2

8 OHM TWINAX CABLE  
ACKET: PVC, BLUE  
OM, DA: 242' [6.15]  
WWW.L-CM.COM  
LCXXXXXX-XX

∠ TRB 2-SI OT PIIG

LC3MSA00571-12 REV 1.0 | © 2020 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.

USA & Canada (800) 341-5266 | International (978) 682-6936 | [l-com.com](http://l-com.com)

## NOTES.

1. CABLE ASSY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROX CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROX 6 INCHES FROM EACH CONNECTOR.  
CABLE ASSEMBLY LENGTH DETERMINED BY ILLUSTRATED.  
LC3MSA00571-XX (-XX = OAL IN INCHES)
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN WHOLE OR IN PART, WHETHER BY MEANS OF PAPER OR ELECTRONIC STORAGE AND RETRIEVAL, IS PROHIBITED.

 <b>L-com</b> <b>an INFINITI® brand</b>		INTERPRET ALL DIMENS. TOLERANCES FOR ASME Y1.10-2009 SHEET 1 OF 1 L3CMSA00571	
<p>UNLESS OTHERWISE SPECIFIED,          LEADING DIMENSIONS ARE IN INCHES          DIMENSIONS IN ITALIC ARE MILLIMETERS</p>			
<p>TOLENCES:</p>			
$X = \pm 2 [5]$ $XX = \pm 0.02 [0.5]$ $XXX = \pm 0.005 [0.1]$		<b>FRACTIONS</b> $\frac{1}{32}$ <b>ANGLES</b> $\pm 1^\circ$	
<p>CABLE LENGTH TOLERANCES:</p>			
$\leq 12 [305] \leq 60 [1524]$ $10 [254] \leq 120 [3048]$ $\leq 60 [1524] \leq 300 [7623]$			
<p><b>DESCRIPTION</b></p>			
<p>Lead Free 2-Slot TRB Plug to Bend Relief 3-Slot TRB Plug 1          Twinax Cable Using 78 Ohm 30-02001-LC</p>			
<p>Website: <a href="http://www.L-com.com">www.L-com.com</a></p>		<p>Phone: 1.800.341.2526   1.979.682.6936</p>	
<p>ITEM NO.</p>		<p>DRAWN BY  <b>KDANG</b></p>	
<p>ALL DIMENSIONS ARE FOR REFERENCE ONLY          AND SUBJECT TO CHANGE WITHOUT NOTICE          UN-DIMENSIONED NON-CRITICAL FEATURES          MAY VARY IN SIZE AND LOC.          COLORS MAY VARY</p>			

1-LC

1

1