

Hand Formable Test Probe SMA Female 2 Hole Flange to Trimmed Lead Cable Assembly using LC047TB Coax, Stainless Steel Body, 3 IN

LCCA30709-3IN



Configuration


- Connector 1: SMA Female 2 Hole Flange
- Connector 2: Trimmed Lead
- Cable Type: LC047TB

Features

- 100% RF Tested prior to final trim
- 1.4 Max VSWR to 18 GHz
- 100% High Pot Tested to 500V
- 0.047 Diameter Formable coax
- Individually packed in protective tube

Applications

- Used as an RF Test Probe to 18 GHz
- RF PCB Board Measurements
- Signal Injection



Description

L-com's LCCA30709-3IN is a Test Probe SMA Female 2 Hole Flange to Trimmed Lead Cable Assembly using LC047TB Coax, 0.25 FT and ships same-day. L-com's formable cable assemblies provide a convenient alternative to their semi-rigid versions, as they offer similar electrical performance but can be bent to desired shape without the use of special tools. Our L-com SMA to pre-trimmed cable assembly has a Female to sexless gender configuration with formable LC047TB series coax and operates to 18 GHz. The tinned copper braid outer conductor can be easily formed by hand and has an overall diameter of 0.047 inches.

The Test Probe SMA Female 2 Hole Flange to Trimmed Lead Cable Assembly using LC047TB Coax, 0.25 FT is a convenient test probe designed to be directly soldered to an exposed microstrip trace to inject a signal or to measure a signal of interest. Each LCCA30709-3IN cable assembly is built with a connector on both ends to verify the electrical performance of 18 GHz with a maximum VSWR of 1.4:1. The cable is then trimmed and placed in a reusable protective tube. These test probes are available with a flush cut or a pre-trimmed cable lead.

Custom versions of this SMA Female to trimmed lead cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30709-3IN L-com Test Probe SMA Female 2 Hole Flange to Trimmed Lead Cable Assembly using LC047TB Coax, 0.25 FT data sheet PDF include details of the RF product specifications, CAD drawing(s) and dimensions below.

Hand Formable Test Probe SMA Female 2 Hole Flange to Trimmed Lead Cable Assembly using LC047TB Coax, Stainless Steel Body, 3 IN

LCCA30709-3IN



Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.4:1	%
Velocity of Propagation		69.5		
Capacitance		32 [104.99]		pF/ft [pF/m]
DC Resistance Inner Conductor		207 [679.13]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		8 [26.25]		Ohms/1000ft [Ohms/Km]

Mechanical Specifications

Cable Assembly

Length	3 in [76.2 mm]
--------	----------------

Cable

Cable Type	LC047TB
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor Material and Plating	Tinned Copper Braid

Connectors

Description	Connector 1	Connector 2
Type	SMA Female 2 Hole Flange	Trimmed Lead
Specification	MIL-STD-348	
Impedance	50 Ohms	
Contact Material and Plating	Beryllium Copper, Gold over Nickel	
Contact Plating Specification	MIL-G-45204	
Dielectric Type	PTFE	
Outer Conductor Material and Plating	Stainless Steel, Gold	
Outer Conductor Plating Specification	MIL-G-45204	
Body Material and Plating	Stainless Steel, Gold over Nickel	
Body Plating Specification	MIL-G-45204	

Hand Formable Test Probe SMA Female 2 Hole Flange to Trimmed Lead Cable Assembly using LC047TB Coax, Stainless Steel Body, 3 IN



LCCA30709-3IN


Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:



Example: LCCA30709-12 = 12 inches long cable
 LCCA30709-100cm = 100 cm long cable

Hand Formable Test Probe SMA Female 2 Hole Flange to Trimmed Lead Cable Assembly using LC047TB Coax, Stainless Steel Body, 3 IN from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Hand Formable Test Probe SMA Female 2 Hole Flange to Trimmed Lead Cable
Assembly using LC047TB Coax, Stainless Steel Body, 3 IN

L-com CAD Drawing

