








THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

DESCRIPTION	MATERIAL	FINISH
MAIN BODY	BRASS	NICKEL
CENTER CONTACT	PHOSPHOR BRONZE	GOLD
OUTER CONTACT	BRASS	NICKEL
FERRULE	BRASS	NICKEL
RETAINING RING	PHOSPHOR BRONZE	-----
INSULATOR	PTFE	-----
GASKET	MVQ	-----

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
C	ECN5321: UPDATED FORMAT AND NOTES. ADDED PACKAGING NOTE.	02/17/2011	
D	ECN 9551: UPDATE DIM'S AND MATERIAL'S	12/09/2018	SLI



NOTES:

ELECTRICAL:

IMPEDANCE: 50 OHMS
 DIELECTRIC WITHSTANDING VOLTAGE: 1000 Vrms
 FREQUENCY RANGE: DC~6 GHz
 VOLTAGE RATING: 500V PEAK
 DURABILITY: ≥ 500 CYCLES
 CABLE RETENTION: 30 POUNDS PULL

MISCELLANEOUS:

CONNECTOR SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY BPUCHASKI	08/21/2009		CATEGORY COAXIAL
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	CHECKED BY M.AUDAS	08/21/2009	PRODUCT DESCRIPTION CON,SMA MALE STRAIGHT CRIMP, LMR195	
	APPROVED BY M.AUDAS	08/21/2009	SIZE A	FSCM NO. 43321
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		DWG. NO. ASM-1708	REV. D
	COLOR VARIATIONS MAY OCCUR	1A801-024	SCALE: NONE	CAD FILE: ASM-1708.SLDDRW
				SHEET 1 OF 1