





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
E	ECN 3155: UPDATE DWG FORMAT	1/18/08	D.GRIFFIN



RECOMMENDED FERRULE CRIMP SIZE. (PIN SHALL BE SOLDERED)



CABLE STRIPPING DIMENSIONS



NOTES:

**MATERIAL:**  
 BODY: BRASS  
 FERRULE: BRASS OR COPPER ALLOY  
 PIN: BRASS  
 INSULATOR: ACETAL


**FINISH:**  
 BODY: NICKEL PLATE  
 FERRULE: NICKEL PLATE  
 PIN: GOLD PLATE

**ELECTRICAL:**  
 IMPEDANCE: 50 OHM

**PACKAGING:**  
 INDIVIDUALLY PACKAGE EACH ASSEMBLY UTILIZING APPROPRIATE SIZED BAG

**APPLICATION:**  
 RG213 COAXIAL CABLE.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  
 TOLERANCES TO BE:  
 .X ±.1 [2.5] ANGLES ±2°  
 .XX ±.01 [.25]  
 .XXX ±.005 [.13]  
 OVERALL CABLE LENGTH TOL:  
 ≤ 60 [1524] +3 [76.2] / -0  
 > 60 [1524] +5% / -0%



APPROVALS	DATE
DRAWN BY C.MCCORMICK	01/30/2004
CHECKED BY D.PARHAN	01/30/2004
APPROVED BY R.CARRICK	01/30/2004

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY COAXIAL		PRODUCT DESCRIPTION CONN TNC M RG213 CRIMP	
SIZE <b>B</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>BAC504</b>	REV. <b>E</b>
SCALE: 1:1		CAD FILE: BAC504.SLDDRW	SHEET 1 OF 1