REVISIONS							
	REV	DESCRIPTION	DATE	APPROVAL			
	Α	DRAWING REPLACES BAK300-OD1	7/3/14	D.FRISIELLO			



DELUXE COAX ADAPTOR KIT

AN EXAMPLE OF A TYPICAL THREE-ELEMENT COMBINATION IS SHOWN BELOW. ANY TWO CONNECTOR ELEMENTS IN A KIT MAY BE JOINED BY SCREWING THEM ONTO A COUPLER ELEMENT.

SMA JACK ELEMENT COUPLER

BNC PLUG ELEMENT







KIT CONSISTS OF 6 IDENTICAL COUPLER ELEMENTS AND ${\bf 2}$ EACH OF THE FOLLOWING CONNECTOR ELEMENTS, A TOTAL OF 30 ELEMENTS.

PLUGS	JACKS			
TYPE "N"	TYPE "N"			
UHF	UHF			
SMA	SMA			
BNC	BNC			
TNC	TNC			
F	F			

NOTES:

ADAPTER KIT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE: CE2011/65/EU(RoHS DIRECTIVE)

	APPROVAIS	DATE				_			
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	DRAWN BY MCCMORMICK	7/21/04	Ŀ	C				NORTH AN	VOOD DRIVE IDOVER, MA
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0	CHECKED BY D.FRISIELLO	7/3/14	CATEGO	DV.		- 00	THI CCCIVICY	01	845
>12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120[3048] - 300[7620] = +6 [152] / -0	APPROVED BY D.FRISIELLO	7/3/14	COAXIAL						
>300[7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 [5.08] .XX = .005 [.13]	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION KIT ADAPTER 108 VARIOUS TYPES						
PROJECTION (+)	COLOR VARIA MAY OCC		SIZE	FSCN 433		DWG. NO.	BAK300)	A REV.
			SCALE: 1:1 CAD FILE: BAK300.SLDDRW			SHEET 1 OF 1			