


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 7237: ADDED CHD26MM-1, ADDED REGULATORY	1/14/14	D. CASTRO
-	-	-	-
-	-	-	-
-	-	-	-



2X, MALE 26 PIN HIGH DENSITY D-SUB CONNECTOR GOLD PLATED PINS

WIRING MAP		
"P1"	COLOR	"P2"
1	BROWN	1
2	RED	2
3	ORANGE	3
4	YELLOW	4
5	GREEN	5
6	BLUE	6
7	VIOLET	7
8	GRAY	8
9	WHITE	9
10	LIGHT GREEN	10
11	BLACK	11
12	GRAY/BLACK	12
13	BLUE/WHITE	13
14	VIOLET/WHITE	14
15	BROWN/WHITE	15
16	BLACK/WHITE	16
17	RED/WHITE	17
18	ORANGE/WHITE	18
19	GREEN/WHITE	19
20	GRAY/GREEN	20
21	GRAY/RED	21
22	GRAY/VIOLET	22
23	LIGHT GREEN/BLACK	23
24	RED/BLACK	24
25	ORANGE/BLACK	25
26	YELLOW/BLACK	26
SHELL	DRAIN WIRE	SHELL

PART NUMBER	LENGTH	
	FEET	METERS
CHD26MM-1	1.0	0.31
CHD26MM-2.5	2.5	0.76
CHD26MM-5	5.0	1.52
CHD26MM-10	10.0	3.05
CHD26MM-15	15.0	4.57

NOTES:

1. CABLE SHALL BE TESTED FOR CONTINUITY.
2. CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ± .005 [1.3]	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY	TJC			8/15/01	
	CHECKED BY	DFP	8/16/01	CATEGORY <b>D-SUBMINIATURE</b>		
	APPROVED BY	RC	8/17/01			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION <b>CABLE, HD26M/M MOLDED</b>	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>CHD26MM</b>	REV. <b>E</b>
COLOR VARIATIONS MAY OCCUR CHD-FS01		SCALE: NONE	CAD FILE: CHD26MM.SLDDRW	SHEET 1 OF 1		