



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE PER BRIAN GATES	03/27/2017	JLABOY
B	ECN 8743: CHANGE PACKAGING SPEC FROM PKG-00012 TO PS-0031	05/01/2017	JLABOY
C	ECN 9053: CREATE 3D MODEL, REVISE DRAWING TO L-COM STANDARDS	01/18/2018	DFRSIELLO
D	ECN 9537: P1 WIRE MAP PIN 6 TO 16, P2 DESCRIPTION TO 24, REMOVE ROHS	11/26/2018	DFRSIELLO



NOTES:

ELECTRICAL PROPERTIES:
 VOLTAGE TEST: DC 300V
 INSULATION RESISTANCE: 10.0M OHM MIN
 CONDUCTIVE RESISTANCE: 2.0 OHM MAX

MISCELLANEOUS:
 INSIDE MOLDED P2 END MUST USE COPPER FOIL AND SOLDER BRAID 360 DEGREE TO THE SHELL
 CABLE ASSEMBLY SHALL BE UL CERTIFIED
 CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [5.1] .XXX = ±.005 [1.3]	APPROVALS	DATE	50 HIGH STREET NORTH ANDOVER, MA 01845	
	DRAWN BY BPUCHASKI	03/27/2017		CATEGORY AUDIO/VIDEO
PROJECTION 	CHECKED BY JLABOY	03/27/2017	PRODUCT DESCRIPTION CA DVI TO DP LSZH 1 FEET	
	APPROVED BY BGATES	03/27/2017		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR
	SIZE A	FSCM NO. 43321	DWG. NO. CTLDVI-DLSP-MM-1	REV. D
	SCALE: NONE		CAD FILE: CTLDVI-DLSP-MM-1.SLDDRW	SHEET 1 OF 1

A

A