



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/17/10	D.GRIFFIN
B	ECN 6914: ADDED DIELECTRIC, ANTENNA ELEMENT, AND GASKET MTL: ROHS	6/20/13	D. DESJARDIN
C	ECN 7972 REMOVE DIM. 826, ADD DIM 1.08	06/01/15	B.PUCHASKI

DESCRIPTION	MATERIAL	FINISH
CONNECTOR	BRASS	GOLD PLATED
CONTACT	BRASS	GOLD PLATED
DIELECTRIC	TEFLON	-
ANTENNA ELEMENT	COPPER	-
GASKET	SILICON RUBBER	-
ANTENNA COVER	TPU	BLACK



RP SMA PLUG  
GOLD PLATED





**NOTES:**

ELECTRICAL:  
 FREQUENCY RANGE: 2.4 GHz (2.4 ~ 2.5GHz)  
 ELECTRIC WAVE: 1/4, MONOPOLE ANTENNA.  
 V.S.W.R.: <2  
 IMPEDANCE: 50 OHM, NOMINAL  
 GAIN: <0 dBi

PACKAGING:  
 COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PKG-00012. BAG LABEL PER L-COM SPEC LSP-010.

**REGULATORY COMPLIANCE:**  
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: <math>\leq 12 [305] = +1 [25] / -0</math> >12 [305] <math>\leq 60 [1524] = +2 [51] / -0</math> >60 [1524] <math>\leq 120 [3048] = +4 [102] / -0</math> >120 [3048] <math>\leq 300 [7620] = +6 [152] / -0</math> >300 [7620] = +5% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	8/16/10	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ± .005 [1.3]	CHECKED BY M.MARTINEZ	8/16/10	CATEGORY <b>ANTENNA</b>
	APPROVED BY K.BLOMGREN	8/16/10	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION <b>ANTENNA STUBBY RP SMA PLUG R.A.</b>	
COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>HG2400RDR90-RSP</b>
SCALE: NONE		CAD FILE: HG2400RDR90-RSP.SLDDRW	SHEET 1 OF 1